

Cell Culture for Education

Description	Cat. No.	Price
Media and Supplements		
MP Biomedicals™ Adult Bovine Serum, 100mL	S35903	\$35.50
Streptomycin Sulfate, 5g	S25797	\$40.00
BD Bacto™ Peptone, 500g	S71604	\$157.00
Ethylenediamine Tetraacetic Acid, 100g	S25311B	\$17.75
EDTA, Disodium Salt, 100g	S25687A	\$39.25
MP Biomedicals Porcine Serum, 100mL	S35905	\$23.75
Methyl Red Indicator, 25g	S25434A	\$21.25
Methyl Red Indicator, 500mL	S25435	\$7.55
Phenol Red Indicator, 500mL	S25464A	\$10.75
Phenol Red Indicator, 10g	S25465	\$18.00
Tris Borate EDTA Buffer, 5X, 500mL	S25616	\$10.75
Sucrose, 500g	S25590	\$13.00
Sucrose, 2.5kg	S25590B	\$36.50
Thermo Scientific™ Magnesium Chloride, 4 x 1.25mL	S35873	\$18.75
Cell Counting		
Fisherbrand™ Counter Pen	S94107	\$22.50
Fisherbrand Digital Key-Chain Wristband Counter	S94108	\$14.75
Hausser Scientific™ Hemocytometer	S17040	\$397.00
Fisherbrand Hand Tally Counter	S90189	\$14.75
United Scientific™ Supplies Hand Tally Counter	S90333	\$12.00
Fixing and Staining		
Formaldehyde Solution, 500mL	S25329	\$17.50
Formalin Solution, 10%, 1L	S25689	\$22.00
Innovating Science™ Formaldehyde Solution Spill Kit	S28498	\$49.50
Bromothymol Blue Solution, 0.04%, 10mL	S25207	\$4.75
Bromothymol Blue Solution, 0.04%, 30mL	S05149	\$5.45



Description	Cat. No.	Price
Thymol Blue, 5g	S25604	\$43.50
Thymol Blue Solution, 0.04%, 100mL	S25605	\$8.70
Toluidine Blue O Solution, 0.5%, 100mL	S25613	\$12.75
Bromphenol Blue Indicator Solution, 0.04%, 100mL	S25848	\$3.80
Alizarin Yellow R, Sodium Salt, 5g	S25133	\$9.50
Alizarin Yellow R, Sodium Salt, 10g	S25133A	\$11.75
Alizarin Yellow R, Indicator Solution, 500mL	S25134	\$17.50
Alizarin Yellow R, Indicator Solution, 100mL	S25134A	\$7.80
Fuchsin Acid, 5g	S25690	\$21.00
Rhodamine B, 25g	S25785	\$40.25
Rhodamine B Staining Solution, 1%, 20mL	S25786	\$12.00
Fluorescein, Disodium Salt, 25g	S25328	\$11.50
Fluorescein, Disodium Salt, 100g	S25328A	\$24.25
Methyl Orange Indicator, 25g	S25433A	\$11.50
Phenolphthalein Indicator, 25g	S25466	\$8.80
Phenolphthalein in IPA Solution, 0.5%, 500mL	S25468	\$7.65
Phenolphthalein in IPA Solution, 1%, 500mL	S25467A	\$7.60
Eosin Yellow in Alcohol Solution, 1%, 100mL	S25303	\$9.45
Alizarin Red S, 25g	S25131	\$15.00
Phenol Solution, 100mL	S25463	\$18.50
Sudan IV in Acetone Solution, 0.05%, 100mL	S25592	\$9.65
EISCO™ Microscope Glass Slides, Plain, 50/Pack	S13943	\$2.40
EISCO Microscope Glass Slides, Frosted, 50/Pack	S13944	\$3.15
EISCO Microscope Cover Glasses, 100/Pack	S13945	\$2.40
GSC Glass Microscope Slides, 144/Pack	S17466A	\$15.50
United Scientific Supplies Coplin Staining Jar, 12/Pack	S17495A	\$32.75
EISCO Glass Staining Trough with Glass Lid	S39744	\$16.00
Culture Tubes and Flasks		
Corning™ PYREX™ Culture Tubes, 6 x 50mm, 0.5mL, 72/Pack	S63293	\$31.25
PYREX Culture Tubes, 10 x 75mm, 3mL, 72/Pack	S63294	\$33.50
PYREX Culture Tubes, 12 x 75mm, 5mL, 72/Pack	S63295	\$41.50
PYREX Culture Tubes, 13 x 100mm, 9mL, 72/Pack	S63296	\$34.83
PYREX Culture Tubes, 16 x 100mm, 11mL, 72/Pack	S63297	\$41.50
PYREX Culture Tubes, 18 x 150mm, 27mL, 72/Pack	S63300	\$68.25
PYREX Culture Tubes, 20 x 150mm, 34mL, 72/Pack	S63301	\$63.50
PYREX Culture Tubes, 22 x 175mm, 50mL, 72/Pack	S63302	\$103.00



Description	Cat. No.	Price
PYREX Culture Tubes, 25 x 200mm, 70mL, 72/Pack	S63304	\$94.00
PYREX Flat-Bottomed Culture Tubes, 25 x 100mm, 39mL, 36/Pack	S67132	\$84.00
Corning™ PYREX™ VISTA™ Culture Tubes, 6 x 150mm, 0.5mL, 50/Pack	S76111M	\$17.25
VISTA Culture Tubes, 12 x 75mm, 5mL, 200/Case	S76111B	\$72.75
VISTA Culture Tubes, 13 x 100mm, 9mL, 50/Pack	S76111C	\$19.50
VISTA Culture Tubes, 16 x 100mm, 11mL, 50/Pack	S76111D	\$23.25
VISTA Culture Tubes, 16 x 125mm, 15mL, 50/Pack	S76111E	\$27.50
VISTA Culture Tubes, 16 x 150mm, 20mL, 50/Pack	S76111F	\$29.25
VISTA Culture Tubes, 18 x 150mm, 27mL, 50/Pack	S76111G	\$30.50
VISTA Culture Tubes, 20 x 150mm, 34mL, 50/Pack	S76111H	\$35.50
VISTA Screw-Capped Culture Tubes, 13 x 100mm, 9mL, 50/Pack	S76112A	\$60.00
VISTA Screw-Capped Culture Tubes, 16 x 100mm, 11mL, 50/Pack	S76112B	\$332.00
VISTA Screw-Capped Culture Tubes, 16 x 125mm, 15mL, 50/Pack	S76112C	\$83.00
VISTA Screw-Capped Culture Tubes, 16 x 150mm, 20mL, 50/Pack	S76112D	\$107.00
VISTA Screw-Capped Culture Tubes, 20 x 125mm, 25mL, 50/Pack	S76112E	\$128.00
VISTA Screw-Capped Culture Tubes, 25 x 150mm, 55mL, 50/Pack	S76112G	\$129.00
Thermo Scientific™ Nunc™ Tissue Culture Flasks, Untreated, 55mL, 30/Case	S04852	\$216.00
Corning™ U-Shaped Tissue Culture Flasks, Treated, 275mL, 10/Pack	S304661	\$33.00
Incubators		
Revolutionary Science Basic Incufridge, 1.2 cu. ft. (33L)	S28415	\$900.00
Revolutionary Science Professional Incufridge, 1.2 cu. ft. (33L)	S28416	\$1,375.00
Revolutionary Science Professional Incufridge, 1.9 cu. ft. (53L)	S28417	\$2,045.00
Revolutionary Science Professional Incufridge, 2.6 cu. ft. (73L)	S28418	\$3,195.00
Fisherbrand™ Mini Low-Temperature Incubator, 0.6 cu. ft. (18L)	S42807	\$599.00
Thermo Scientific™ Heratherm™ GP Microbiological Incubator, 2.6 cu. ft. (75L)	S37377	\$2,107.00
Heratherm GP Microbiological Incubator, 4.1 cu. ft. (117L)	S37378	\$2,599.00
Heratherm GP Microbiological Incubator, 6.9 cu. ft. (194L)	S37379	\$3,020.00

Visit fisheredu.com/biotechproducts to find more cell culture products like these for your school's laboratory.

In the United States:

For customer service, call 1-800-955-1177
 To fax an order, use 1-800-955-0740
 To order online: fisheredu.com

Fisher Science Education

4500 Turnberry Drive
 Hanover Park, IL 60133

