







Nitrile Exam Glove Comparison Chart

	Glove Style Packaging Fisher Scientific Cat. No.	Typical Values Thickness Length Weight	Chemotherapy Drug Permeation Tested ASTM D6978 USP <800> Compliant	Material	ISO 374-1:2016 Chemical Protection (Formerly EN 374-3:2003)	ISO 374-5:2016 Protection Against Bacteria, Fungi and Virus (Formerly EN 374-2:2003)
RoyalTouch300™	 300 Box/3000 Case (XL 250/Box) 18-041-140 to 18-041-144 (XS - XL)	Palm 2.3 - 2.7 mils Finger 3.9 - 4.3 mils 9.5" Length 3.0 grams	YES	Nitrile	TYPE B K P T	PASSED
Sable600™	 300 Box/3000 Case (XL 250/Box) 17-010-396 to 17-010-400 (XS - XL)	Palm 2.3 - 2.7 mils Finger 3.9 - 4.7 mils 9.5" Length 3.2 grams	YES	Accelerator-Free LOW DERMA™ Nitrile Fentanyl Permeation Tested ASTM D6978 >240 Minutes Fentanyl Citrate Injection (100mcg/2ml)	TYPE B K P T	PASSED
Scion700™	 300 Box/3000 Case (XL 250/Box) 17-900-912 to 17-900-916 (XS - XL)	Palm 2.3 - 2.7 mils Finger 3.9 - 4.7 mils 9.5" Length 3.2 grams	YES	Accelerator-Free LOW DERMA™ Nitrile Fentanyl Permeation Tested ASTM D6978 >240 Minutes Fentanyl Citrate Injection (100mcg/2ml)	Type B K P T	PASSED
Fortis500™ Extended Cuff	 100 Box/1000 Case (XL 90/Box) 17-900-927 to 17-900-932 (XS - XXL)	Palm 3.5 - 3.9 mils Finger 5.1 - 5.5 mils 10.5" Length 5.0 grams	YES	Accelerator-Free LOW DERMA™ Nitrile Fentanyl Permeation Tested ASTM D6978 >240 Minutes Fentanyl Citrate Injection (100mcg/2ml)	TYPE B K P T	PASSED
FreeStyle1100™	 100 Box/1000 Case (XXL 80/Box) 19-423-006 to -010 (XS - XL) -016 (XXS) 15-423-050 (XXL)	Palm 2.3 - 2.7 mils Finger 3.9 - 5.1 mils 9.5" Length 3.7 grams	YES	Accelerator-Free LOW DERMA™ Nitrile Fentanyl Permeation Tested ASTM D6978 >240 Minutes Fentanyl Citrate Injection (100mcg/2ml)	TYPE B K P T	PASSED
AirSoft900™	 100 Box/1000 Case 19-423-001 to 19-423-005 (XS - XL)	Palm 2.7 - 3.1 mils Finger 4.7 - 5.5 mils 9.5" Length 4.2 grams	YES	Nitrile	TYPE B K P T	PASSED

All HandPRO® brand gloves are safe for food contact.

Hourglass-Intl.com | 800-277-0994

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437



part of Thermo Fisher Scientific