

Catalog Number	15-077-720	06-664-270	15-077-721	15-078-215 15-078-176	15-081-106	15-081-110	15-081-123 15-081-124	15-081-134 15-081-130
CDC Requirements								
Traceable® Certificate supplied	✓	✓	✓	✓	✓	✓	✓	✓
Calibration Report Included	✓	✓	✓	✓	✓	✓	✓	✓
Annual Recalibration by ILAC/MRA accredited laboratory available	✓	✓	✓	✓	✓	✓	✓	✓
CDC Recommendations								
Glycol encased probe	✓	✓	✓	✓	✓	✓	✓	✓
Certificate of Calibration includes methods and procedure documentation	✓	✓	✓	✓	✓	✓	✓	✓
Certificate of Calibration includes stated uncertainties	✓	✓	✓	✓	✓	✓	✓	✓
Certificate of Calibration includes measurement results	✓	✓	✓	✓	✓	✓	✓	✓
Minimum/Maximum Memory	✓	✓	✓	✓	✓	✓	✓	✓
Capable of displaying current temperature and minimum/maximum memories	✓	✓	✓	✓	✓	✓	✓	✓
Minimum/Maximum Memory reset	✓	✓	✓	✓	✓	✓	✓	✓
Detachable probe	✓	✓	✓	✓	✓	✓	✓	✓
High/Low Alarm	✓	✓	✓	✓	✓	✓	✓	✓
Read storage unit temperatures without opening the door	✓	✓	✓	✓	✓	✓	✓	✓
±0.5°C (±1°F) Accuracy	±1°C	±1°C	±0.5°C	±0.3°C	±0.1°C	±0.5°C	±0.25°C	±0.25°C
Low battery indicator	✓	✓	✓	✓	✓	✓	✓	✓
Data Logger with Continuous Monitoring and Active Display					✓	✓	✓	✓
Data Logger with user programmable logging intervals						✓	✓	
Data Logger capable of storing 4,000 readings that will not overwrite when full						✓		✓