

# Soft-Sided Table Top Heating Mantles



## PRODUCT HIGHLIGHTS:

- Self-supporting: Can be placed directly on counter top
- Silicone impregnated fiberglass outer shell
- Easy viewing of flask contents
- Operation temperatures up to 482°C (900°F)
- Multi-strand resistance wire for increased durability
- 120 VAC model includes 3" (76 mm) lead wire with NEMA 1-15R connector and a 4' (1.2 m) power adapter cord with NEMA 1-15 plug
- 240 VAC model includes 3" (76 mm) lead wire with no plug



## ORDERING INFORMATION

### 120 VAC

Size mL	Watts	Part Number	Catalog Number
50	52	FHM0050VF1	11476034
100	70	FHM0100VF1	11476035
250	143	FHM0250VF1	11476036
500	210	FHM0500VF1	11476037
1000	377	FHM1000VF1	11476038
2000	520	FHM2000VF1	11476039
3000	550	FHM3000VF1	11476040
5000	620	FHM5000VF1	11476041

### 240 VAC

Size mL	Watts	Part Number	Catalog Number
50	52	FHM0050VF2	11476042
100	70	FHM0100VF2	11476043
250	143	FHM0250VF2	11476044
500	210	FHM0500VF2	11476045
1000	377	FHM1000VF2	11476046
2000	520	FHM2000VF2	11476047
3000	550	FHM3000VF2	11476048
5000	620	FHM5000VF2	11476049

\*Temperature controller required for safe operation of this product

Contact us today:

#### In the United States

Order online: [fishersci.com](http://fishersci.com)  
 Fax an order: 1-800-926-1166  
 Call customer service: 1-800-766-7000

#### In Canada

Order online: [fishersci.ca](http://fishersci.ca)  
 Fax an order: 1-800-463-2996  
 Call customer service: 1-800-234-7437

