

Safety

2024 Product
Catalog

 **fisher science**
education
part of Thermo Fisher Scientific

Featured Suppliers



Visit fisheredu.com/featuredsuppliers to learn more about these suppliers and their products.

Helpful Icons



New product



Must be shipped by truck for regulatory reasons



Meets Americans with Disabilities Act requirements



Protects against splashes from hazardous chemicals or potentially infectious materials



Applicable for remote learning



Defined as a medical device by the FDA

Guarantee

If you're not 100% satisfied with your purchase, contact our customer service team within 30 days of your invoice date and we'll either exchange, repair, or replace the product, or give you a credit for the full purchase price. Call us toll-free for a return authorization number.

Special order items, furniture, and closeouts cannot be exchanged or credited.

Phone: 1-800-955-1177 • 7 a.m. to 5:30 p.m.
Central Time, Monday through Friday

Fax: 1-800-955-0740 • 24 hours a day, 7 days a week

Email: fse.custserv@thermofisher.com

Website: fisheredu.com

Address: Fisher Science Education
4500 Turnberry Drive
Hanover Park, IL 60133

For international orders, see page 40.

Products featured in this catalog may have limited availability and extended lead times. Prices are subject to change.

Connect with Us on Social Media



fisheredu.com/facebook



pinterest.com/fishersciedu

Safety

Preparing today's students to be the innovators of tomorrow isn't always easy, but finding the right teaching tools can be. From basic lab supplies to state-of-the-art classroom technology, the Fisher Science Education team has everything you need to create a 21st century STEM learning environment.

Visit fisheredu.com to get started.

Want to customize aspects of your curriculum?

Explore custom kits to meet the unique demands of your classroom. Visit fisheredu.com/customkitting to learn more.

Concerned about shipping and handling fees?

We offer \$12 flat-rate shipping on most orders and our hazardous material fee is just \$15 — the lowest in the country.

Looking for Something Else?

Check out our other 2024 catalogs:

- Chemicals
- Lab furniture and equipment
- Lab supplies and consumables
- Life sciences
- Physical science
- STEM



Carbon forms more compounds than any other element, and it's in millions of substances ranging from pencil graphite you can hold in your hand to a diamond ring you can wear on your finger.

Visit fisheredu.com/headlinediscoveries for more articles and information for your classroom.

Fire, Emergency & First Aid

Fire	6
Emergency & First Aid	6

Personal Protective Equipment

Face and Eye Protection	12
Hand Protection	16
Aprons & Lab Coats	17

Facilities

Signage	23
Social Distancing Aids	25
Cleaners and Sanitizers	26
Sinks and Eyewash Stations	28
Safety Cans	28
Storage Cabinets	30

Visit fisheredu.com to view our full offering of products.

Shake-Up Your Workflow with Baths, Mixers, and More



Flexible Digital Dry Baths

Increase lab versatility with Thermo Scientific™ digital dry baths, offered in a range of configurations for a variety of application needs.

Cat. Nos. S37337, S37338



Aluminum Dry Bath Blocks

Support your workflow with Fisherbrand™ dry bath blocks for Fisherbrand™ Isotemp™ Digital Dry Baths/Block Heaters.

Cat. Nos. S30223, S30224

Precise, Flexible Hotplates & Stirrers

Enhance safety and temperature performance for routine protocols with Thermo Scientific™ Cimarec+™ hotplates and stirrers.



Ordering information

Description	Material	Cat. No
Hot Plate, Ambient to 400°C	Ceramic, EMD	S28878
Hot Plate, Ambient to 540°C	Ceramic, EMD	S28874
Hot Plate, Maximum Temperature 540°C	Ceramic	S28432
Stirrer, Stirring Hotplate, Ambient to 540°C	Ceramic	S28433
Hot Plate Stirrer, 540°C	Aluminum	S28875



Monitor Speed and Time with the Digital Vortex Mixer

Accurately and efficiently mix samples with the Thermo Scientific™ 120 V Digital Vortex Mixer, complete with a digital speed and time display.

Cat. No. S81141

Chemical and Corrosion Resistant Water Baths

Support a range of applications with Thermo Scientific™ Precision™ general purpose and circulating water baths, designed to maintain temperatures from ambient to 100°C.



Water Baths

Description	Capacity	Cat. No
General Purpose Baths	2 L	S37361
Shallow General Purpose Water Bath	2 L	S37362
General Purpose Water Bath	5 L	S37363
General Purpose Water Bath	10 L	S37364
General Purpose Water Bath	20 L	S37365
General Purpose Water Bath	28 L	S37366
Dual General Purpose Water Bath	15 L	S37367
Circulating Water Bath	19 L	S37372
Circulating Water Bath	35 L	S37373



Clear and Chemical Resistant

Enhance laboratory safety with aprons that are resistant to lab chemicals, acids, and more.

Description	Quantity	Size	Cat. No.	Price
Chemical Resistant Translucent Aprons	250/Pack	30 x 24 in.	S139068	\$4.40
	200/Pack	36 x 27 in.	S139069	\$5.05
	180/Pack	42 x 27 in.	S139070	\$5.15
	250/Pack	42 x 35 in.	S139071	\$5.95
	160/Pack	46 x 36 in.	S139072	\$6.10



Responsible Waste Disposal

Dispose of biohazard waste responsibly with steam-autoclavable, tear-resistant polypropylene bags labeled with a black biohazard symbol.

Description	Size	Cat. No.	Price
United Scientific™ Biohazard Disposable Bags	18 x 12 in.	S139248*	\$54.50
	24 x 12 in.	S139249*	\$65.50
	22 x 18 in.	S139250*	\$80.00
	24.5 x 16 in.	S139251*	\$73.00
	35 x 25 in.	S139252*	\$153.00
	31.5 x 24 in.	S139253*	\$167.00
	42 x 42 in.	S139254*	\$167.00



Safeguard Small Hands

Help keep student hands safe during lab time with ambidextrous, beaded-cuff gloves designed for enhanced tactile sensitivity.

Description	Size	Cat. No.	Price
Fisherbrand™ Comfort Nitrile Exam Gloves, 200/Pack	XS	S66653	\$31.50
	S	S05009A	\$31.50
	M	S05009B	\$31.50
	L	S05009C	\$31.50
	XL	S66654	\$31.50



Durable Eye Protection

Protect your students and staff with safety goggles that are flexible and designed for comfort.

Description	Cat. No.	Price
United Scientific Safety Goggles, Plastic, Child Size	S89565	\$2.90
Perforated Safety Goggles	S01256	\$2.00

Fire, Emergency & First Aid

Fire

Bel-Art™ Fire Blanket

Extinguishes small class A, light oil and grease fires without the mess of foam or chemical agents. An excellent supplement to existing safety equipment.

- For small Class A oil/grease fires and flare-ups
- May also be wrapped around the head and body for protection against flames and embers when fleeing a burning room, or for protection from splashing molten metal
- Woven fiberglass with a textured surface; all edges are serged with fireproof Kevlar™ thread
- Close weave greatly reduces the amount of atmospheric oxygen available to feed the fire
- Packaged in an instant access container that can be hung on the wall or stored in any accessible location



Cat. No.	Size	Price
S43321	36 x 40 in.	\$211.00/Ea

Emergency Fire Blanket

Lightweight and easy to apply.

- Smothers clothing fires and other small fires
- Made of fiberglass and hemmed on all four sides with Kevlar™ thread
- Brass grommets on corners
- Machine washable
- 1.5 x 1.8m (5 x 6 ft.)
- Red, heavy-duty vinyl pouch protects blanket from exposure to UV rays, chemicals, moisture dust, salt air, insects, and temperature extremes
- Use for rescue operations in offices, industries and hospitals: either to cover the fire, cutting off the oxygen supply or to wrap around a person whose clothes are on fire



Cat. No.	Price
S47559B	\$190.00/Ea

Evacuation Stair Chair

Delivers universal evacuation solutions for emergencies such as fires, floods, earthquakes, power outages and more.

- For transport up or down stairways.
- Foldable for easy storage
- Lightweight construction
- Heavy-duty wheels
- Lockable rear wheels
- Wall mounting bracket
- Adjustable patient head restraint
- Friction tracks
- Ergonomic adjustable handle
- Quick-release safety belts (head, chest, thigh)
- Reflective decals
- Dual-position seating
- Vinyl storage cover
- Instructional DVD and user guide
- Photo-luminescent indicator sign



WARRANTY: Limited lifetime warranty

Cat. No.	Description	Weight Capacity	Price
S72764	Model 300H MK4 Evacuation Stair Chair	400 lb.	\$1,640.00/Ea

Emergency & First Aid

AED Plus™ Fully Automatic Defibrillator Packages

Provides Real CPR Help™ for rate and depth of chest compressions.

The AED Plus™ is the first and only full-rescue public access AED that provides Real CPR Help for rate and depth of chest compressions. Real-time feedback helps rescuers provide the best manual CPR possible in a sudden cardiac arrest (SCA).



Cat. No.	Includes	Price
S38751	Fully automatic AED Plus with AED cover, PlusTrac Professional5, CPR-D-padz electrode, pack of 10 batteries, and carry case	\$3,657.00/Ea
S38749	Fully automatic AED Plus with AED Cover, PlusRX medical prescription, CPR-D padz electrode, pack of 10 batteries, and carry case	\$2,974.00/Ea
S38750	Fully automatic AED Plus with AED Cover, PlusTrac Professional1, CPR-D-padz electrode, pack of 10 batteries, and carry case	\$3,212.00/Ea

Electrodes for AED Plus™ Defibrillators



For complete CPR and defibrillation delivery.

- Adult electrode: For use on adult patients and children over the age of 8 or more than 55 pounds
- Child electrode: For use with patients under the age of 8 years or less than 55 pounds

Cat. No.	Shelf Life	Product Type	Price
S38752	5 Years	CPR-D-padz™ adult electrode	\$335.00/Ea
S38753	2 Years	Pedi-padz II child electrode	\$189.00/Ea

Disposable Alcohol Swabs

Easy to open and ready to use.

Be sure you always have a good supply of double-thick alcohol pads on hand for blood collecting. Impregnated with 13 mL of isopropyl alcohol, these pads come individually sealed in foil envelopes.



- Dimensions: 1.2 x 1.6 in. (3 x 4 cm)
- Package of 100

Cat. No.	Price
S17032	\$14.50/Pk

Adhesive Bandages

Easy handling and application.

- Easy to open, even with gloved hands
- Just pull firmly on the ends to release the outer wrap
- Apply the bandage directly without touching the pad or the wound
- Each bandage individually wrapped and sterile



Cat. No.	Dimensions (L x W)	Product Type	Price
S47527A	0.75 x 3 in.	Sheer Bandage	\$19.25/Pk
S47527B	1 x 3 in.	Sheer Bandage	\$21.00/Pk
S47527C	0.75 x 3 in.	Flex Bandage	\$20.75/Pk
S47527D	1 x 3 in.	Flex Bandage	\$17.75/Pk

fisherbrand Latex-Free Cohesive Flexible Bandages, Assorted Colors



Flexible bandages are free of natural rubber proteins and allergens.

- Maintain consistent compression without slipping or restricting mobility
- High porosity, water-resistant
- Lightweight, porous material allows skin to breathe for ultimate comfort
- Adhere to themselves — no clips or fasteners needed
- Available in a wide range of colors and widths
- Length: 5 yd. (4.6 m)
- Case of 30

Cat. No.	Price
S25053	\$67.75/Cs

Bandage Scissors, Stainless Steel



Designed for sizing bandages and dressings, and cutting through bandages and medical gauze.

Cat. No.	Item Description	Price
S72160	One Big Ring	\$8.70/Ea
S72161	Black Oxide Coating	\$8.90/Ea

Mini-Bandage Scissors

Scissors are 3.5 in. long with sharp blades.



Cat. No.	Description	Price
S72159	Mini-Bandage Scissors	\$2.85/Ea

Log in to your account on **fisheredu.com** to see your discounts.

FISHER SCIENCE EDUCATION
MAKING SCIENCE MATTER

Visit us online at **fisheredu.com** to learn more about our programs, services and resources.

MobileAid™ Pro 100 Easy-Roll™ High-Visibility Trauma First Aid Station

Rolling high-visibility first aid bag with flag, stretcher, and 5 clear-view organizer boxes.

- Includes an integrated gear and seating platform, 5 clear-view organizer boxes, utility pouches with customizable handle IDs and clear vinyl lids for easy supply identification, an 8-foot extendable first aid flag, and flexible evac stretcher



Cat. No.	Description	Price
S29596	Model 100 Clear Organizer Boxes	\$399.00/Ea

MobileAid™ Pro 200 Easy-Roll™ High-Visibility Trauma First Aid Station

Rolling high-visibility first aid bag with flag, stretcher, and 5 clear-view organizer boxes.

- Includes an integrated gear and seating platform, 5 Quick-Access utility pouches with customizable handle IDs and clear vinyl lids for easy supply identification, an 8-foot extendable first aid flag, and flexible evac stretcher



Cat. No.	Description	Price
S29597	Model 200 Organizer Pouches	\$449.00/Ea

MobileAid™ Modular Trauma First Aid Stations

Roll your trauma first aid supplies, and be ready to respond to any medical emergency.

S29595: Hi-Visibility 260-piece mobile Modular Trauma First Aid Station

Includes:

- 5 Quick-Access first aid supply modules
- Crush-resistant frame
- Flexible stretcher
- First aid flag
- Flashing wheels
- High-visibility reflective safety stripe



- Integrated seat and gear platform.
- OSHA compliant: ANSI/ISEA Z308.1-2015 Class A, Type II first aid kit

S29685 and S29684: First Aid Stations with Bleeding Control Kits

Extensive 260-piece mobile Modular Trauma First Aid Station with an additional Bleeding Control Kit for greater ability to treat bleeding wounds from accidents, disasters, or active shooter situations. This compact dual-wheel mobile station is organized in quick-response first aid modules for rapid response and treatment.

Includes:

- MobileAid™ BleedStop Compact Bleeding Control Kit
- Tourniquet
- Mini-compress bandage
- QuickClot blood clotting gauze
- Petroleum gauze for chest wounds
- Other bleeding wound supplies
- Flexible evacuation stretcher
- First Aid Flag Integrated seat and gear platform

S29686, S29687, and S29688: First Aid Stations with Four Bleeding Control Kits

Extensive 260-piece mobile Modular Trauma First Aid Station with 4 additional Bleeding Control Kits to treat bleeding wounds from accidents, disasters, or active shooter situations.

Includes:

- Compact dual-wheel mobile station organized in quick-response first aid modules for rapid response and treatment
- Includes a flexible evacuation stretcher and First Aid flag
- Integrated seat and gear platform allow patient to sit and be treated or can be used to haul additional equipment (e.g. AED)

Cat. No.	Description	Price
S29595	Modular Trauma First Aid Station	\$599.00/Ea
S29684	Modular First Aid Station with BleedStop Compact 100 Bleeding Control Kit (SWAT-T Tourniquet)	\$709.00/Ea
S29685	Modular First Aid Station with BleedStop Compact 100 Bleeding Control Kit (SOFT-W Tourniquet)	\$746.00/Ea
S29686	Modular First Aid Station with 4 BleedStop 100 Bleeding Control Kits (SWAT-T Tourniquets)	\$1,159.00/Ea
S29687	Modular First Aid Station with 4 BleedStop 200 Bleeding Control Kits (SOFT-W Tourniquets)	\$1,280.00/Ea
S29688	Modular First Aid Station with 4 BleedStop 300 Bleeding Control Kits (SOFT-W Tourniquets & Chest Seals)	\$1,399.00/Ea

MobileAid™ Easy-Roll™ Emergency Incident Command Station

Supplied in grab-and-go pouches.

- For a 4-person team
- Includes supplies for a command shelter as well as for individual team members
- Includes safety vest, N95 mask, whistle, two-way radio, pen writing tablet, leather-palm gloves, flashlight, batteries, light stick, poncho, emergency blanket, and caution tape



Cat. No.	Price
S29608	\$849.00/Ea

MobileAid™ Reflex 200 Hi-Visibility Trauma First Aid Backpack Kit

A 218-piece trauma first aid kit with supplies packed in 3 OTS (over-the-shoulder) medical supplies clear-view pouches with organizer trays and 2 small clear-view pouches.

- Includes a high-visibility safety vest
- Carried in a lightweight MobileAid Reflex backpack



Cat. No.	Price
S29610	\$394.00/Ea

MobileAid™ XL™ Trauma First Aid Backpack Kits

Both kits include a flexible stretcher and ID placards.

- **S29612:** High-capacity first aid backpack with supplies (260 pieces) in clear-view organizer boxes. Includes a flexible stretcher and ID placards
- **S29611:** High-capacity first aid backpack with trauma first aid supplies (260 pieces) in pouches with organizer trays.



Cat. No.	Description	Price
S29612	XL 100 Trauma First Aid Backpack Kit	\$499.00/Ea
S29611	XL 200 Trauma First Aid Backpack Kit	\$604.00/Ea

MobileAid™ BleedStop™ Bleeding Control and Gunshot Wound Trauma First Aid Kits

Immediately treat bleeding wounds from accidents, disasters, or shootings with tourniquets, trauma dressings, chest seals, and other essential bleeding control supplies.

BleedStop COMPACT 100 Bleeding Control and Gunshot Wound Trauma First Aid Kit (S29600)

- Supplied in a SecureLock clear plastic bag
- Includes SWAT-T tourniquet, mini-compress bandage, hemostatic blood clotting gauze, petroleum gauze for chest wounds, and other bleeding wound supplies
- Treats 1 bleeding wound

BleedStop IMMEDIATE RESPONSE 200 Bleeding Control and Gunshot Wound Trauma First Aid Kit (S29601)

- Single Bleeding Wound Trauma Kit supplied in an clear-view ballistic nylon pouch
- Includes SOFT-W tourniquet, mini-compress bandage, hemostatic blood clotting gauze, petroleum gauze for chest wounds, and other bleeding wound supplies
- Treats 1 bleeding wound

BleedStop DOUBLE 300 Bleeding Control and Gunshot Wound Trauma First Aid Kit (S29602)

- BleedStop DOUBLE bleeding control trauma first aid kit includes TWO SOFT-W tourniquets, BloodStopper compress bandages, chest seals, and petroleum gauze pads for torso wound.
- Treats 2 bleeding wounds
- Allows response to multiple casualties simultaneously



Cat. No.	Description	Price
S29600	BleedStop Compact 100	\$98.00/Ea
S29601	BleedStop Immediate Response 200	\$148.00/Ea
S29602	BleedStop Double 300	\$320.00/Ea

Evacuation and Shelter-In-Place Emergency Kits

Emergency kits that are equipped with essential emergency supplies that can last for the first several hours of an emergency.

S29587:

Emergency kit for up to 10 people come equipped with essential emergency supplies that can last for the first several hours of an emergency.

- Designed for small offices and work groups
- Packed in a durable duffel bag for easy storage and contains a carry-flat toilet that fits in the duffel
- Includes emergency instructions, search and rescue supplies and tools, dust masks for easier breathing, first aid, water (5 year shelf life), and items that provide warmth, shelter, communication, light and sanitation

S29583: Classroom lockdown emergency kit with supplies for 25 students and 1 teacher for first several hours after an emergency or disaster.

- Comes in a sealed bucket that converts to a toilet
- Meets the immediate needs of up to 25 students and 1 teacher for the first several hours after an emergency or disaster
- Includes supplies for breathing protection, hydration, first aid, warmth and shelter, communication and light, hygiene and sanitation, and search and rescue

S29588: Emergency kit with supplies for up to 25 people that is designed to last for the first several hours after an emergency or disaster

- Storage bucket converts to an emergency toilet
- Includes emergency instructions, search and rescue supplies and tools, dust masks for easier breathing, first aid, water, and items that provide warmth, shelter, communication, light, and sanitation



Cat. No.	Description	Price
S29587	10-Person Office Evacuation and Shelter-in-Place Emergency Kits	\$199.00/Ea
S29583	25-Student Classroom Lockdown and Emergency Response Kit	\$209.00/Ea
S29588	25-Person Shelter-in-Place Emergency Kit	\$208.00/Ea

Extended Emergency Support Kits

Compact survival kit with supplies for up to 24 hours of emergency support.

S29589: 10-person Compact survival kit with supplies for 24 hours of emergency support for up to 10 people.

- Use as a companion kit to the 10-Person Office Emergency Kit
- Includes water, food, light sticks, and emergency thermal blankets
- Carry box has a handle and is stackable



S29590: Compact, waterproof emergency kit for up to 25 people comes equipped with supplies for a full 24 hours of emergency shelter-in-place support.

- Includes water, water purification tablets, food, light sticks, and emergency thermal blankets

S29584: Compact classroom emergency kit extends the supplies available for up to 25 students and 1 teacher in an emergency that lasts beyond a few hours.

- Includes supplies for a full 24 hours: food, water, water purification tablets, light sticks, and emergency blankets.

Cat. No.	Description	Price
S29589	Emergency Support Kit for 10 people, 24 hrs.	\$132.00/Ea
S29590	Support Shelter-in-Place Kit for 25 people, 24 hrs.	\$193.00/Ea
S29584	Extended Support Emergency Kit for 25 students and 1 teacher, 24 hrs.	\$193.00/Ea

Complete 25-Person Shelter-In-Place Combo Emergency Kits

Emergency kits with preparedness supplies for 25 people is equipped with enough supplies to last from 24 hours to three days after an emergency or disaster.



- Includes emergency instructions, search and rescue supplies and tools, dust masks for easier breathing, first aid, water, water purification tablets, food, and items that provide warmth, shelter, communication, light, and sanitation
- Storage bucket converts to emergency toilet

Cat. No.	Description	Price
S29591	24-hour Shelter-in-Place Kit	\$403.00/Ea
S29592	2-Day 25 person Shelter-in-Place Kit	\$597.00/Ea
S29593	3-Day Shelter-in-Place Emergency Kit	\$791.00/Ea

SchoolGuard™ Hi-Visibility Teacher and Staff School Emergency Kit



Includes a Bleeding Control Kit for treating bleeding wounds from accidents, disasters, or active shooter situations. Stores compactly on shelves or in drawers or cabinets.

Includes:

- MobileAid™ BleedStop Bleeding Control Kit
- Tourniquet
- Mini-compress bandage
- QuickClot blood clotting gauze
- Petroleum gauze for chest wounds
- Other bleeding wound supplies
- Identification
- Communication
- Breathing protection
- Light

Cat. No.	Description	Includes	Price
S29689	BleedStop Compact 100 Bleeding Control Kit	SWAT-T tourniquet	\$179.00/Ea
S29690	BleedStop Compact 200 Bleeding Control Kit	SOFT-W tourniquet	\$199.00/Ea

SchoolGuard™ Hi-Visibility Classroom Evacuation and Lockdown Kit



This high-visibility school emergency kit for up to 29 students and 1 teacher meets all 10 essential survival needs for lockdown or evacuation. Kit includes a Bleeding Control Kit for treating bleeding wounds from accidents, disasters, or active shooter situations.

Includes:

- MobileAid™ BleedStop Bleeding Control Kit
- Tourniquet
- Mini-compress bandage
- QuickClot blood clotting gauze
- Petroleum gauze for chest wounds
- Other bleeding wound supplies
- Portable fold-flat toilet stores in the survival backpack with other survival supplies: water, food, breathing protection, first aid, shelter, warmth, communication, light, tools, and sanitation/hygiene.

Cat. No.	Description	Includes	Price
S29691	BleedStop Compact 100 Bleeding Control Kit	SWAT-T tourniquet	\$396.00/Ea
S29692	BleedStop Compact 200 Bleeding Control Kit	SOFT-W tourniquet	\$426.00/Ea

SchoolGuard™ Easy-Roll Classroom Evacuation and Lockdown Kit



This Easy-Roll high-visibility school emergency kit for up to 29 students and 1 teacher meets all 10 essential survival needs for lockdown or evacuation and includes a Bleeding Control Kit for treating bleeding wounds from accidents, disasters, or active shooter situations.

Includes:

- MobileAid™ BleedStop Compact Bleeding Control Kit
- Tourniquet
- Mini-compress bandage
- QuickClot blood clotting gauze
- Petroleum gauze for chest wounds
- Bleeding wound supplies
- Portable fold-flat toilet stores in the survival backpack with other survival supplies: water, food, breathing protection, first aid, shelter, warmth, communication, light, tools, and sanitation/hygiene

Cat. No.	Description	Includes	Price
S29693	BleedStop Compact 100 Bleeding Control Kit	SWAT-T tourniquet	\$475.00/Ea
S29694	BleedStop Compact 200 Bleeding Control Kit	SOFT-W tourniquet	\$509.00/Ea

N95 Particulate Respirators 8210

Lightweight disposable particulate respirator designed to provide protection against certain non-oil based particles in applications such as grinding, sanding, sweeping, sawing, bagging or other dusty operations.



- At least 95% NIOSH tested filter efficiency for use where solids or non-oil-based liquid aerosols are present
- Synthetic elastic headband
- Adjustable nose clip provides custom fit and reduces the potential for eyewear fogging
- Soft nose foam
- Must be used in accordance with OSHA regulations and the user instructions, warnings and limitations
- Compatible with a variety of protective eyewear and hearing protection
- Helps reduce inhalation exposures to certain airborne biological particles (examples: mold, Bacillus anthracis, Mycobacterium tuberculosis)
- Cannot eliminate the risk of contracting infection, illness or disease
- Package of 20

Cat. No.	Price
S47062A	\$23.25/Pk

Personal Protective Equipment

Face and Eye Protection

Eisco™ Disposable Pleated Face Masks

Feature secure elastic earloops

- Packs of 50



Cat. No.	Size	Price
S27422	Standard	\$50.50/Pk
S27423	Small	\$52.00/Pk

Eisco™ Polycarbonate Safety Shield

Includes adjustable outer panels to accommodate a variety of lab set ups.

- The width of the outer panels is about 8.9 in. (22.5 cm) and the center panel is 11.8 in. (30 cm) wide
- All panels are 4 mm thick and provide excellent visual clarity
- Adjustable
- For classrooms and labs
- Provides clear, easy viewing during experiments
- Mounting clamps are not required for use, but will add stability (not included)



WARRANTY: 1-year limited manufacturer warranty

Cat. No.	Price
S41719	\$121.00/Ea

Eisco™ Safety Face Shield

Fits securely to deep molded brow guard with adjustable crown strap for protection against chemical splashes, and impact from flying objects.

- For use in any home, school, or professional laboratory
- Fits securely to deep molded brow guard with adjustable crown strap
- Protects against chemical splashes and impact from flying objects
- Steel bound plastic visor
- Dimensions (L x W): 7 x 8 in.
- Non-flammable



Cat. No.	Price
S27083	\$12.75/Ea

fisherbrand Disposable Face Shields

High-quality, optically clear, distortion-free 7mil film.

- Polyester lens is treated with antifog and antistatic coating
- Headpiece is held in place by a stretch strap and includes a latex-free foam band for comfortable extended wear
- Package of 25



COMPLIANCE: Conform to OSHA 29CFR Part 1910.1030 for bloodborne pathogens and the CDC's recommendations for protective eyewear.

Cat. No.	Model	Price
S98127	Full face	\$58.00/Pk

Disposable Masks Zero Waste Box™

Recycle disposable masks. Each box includes signage, a built-in liner, shipping to and from your location, and processing of the materials.

How to use:

- Select a Zero Waste Box for a specific waste stream and place your order
- Collect the accepted items to fill the system
- Send it back to TerraCycle with the prepaid return label on your system
- Order your next Zero Waste Box system to continue to recycle
- **Includes:** one Zero Waste Box system, one prepaid return label affixed to your box, outbound shipping to your location, processing and recycling of the materials, customer support from TerraCycle's team of experts
- **Types of masks that can be included:** disposable face masks, including N95, KN95, 3-ply nonwoven, and dust masks; cannot include paper masks or reusable fabric masks

⚠️ ALERTS: Not available in Hawaii, Alaska, and Puerto Rico.



Cat. No.	Dimensions (L x W x H)	Capacity (Metric)	Price
S88854115	11 x 11 x 20 in.	39.66 L	\$133.00/Ea
S88854116	11 x 11 x 40 in.	79.31 L	\$202.00/Ea

fisherbrand 200 Series Safety Glasses



**Economical,
lightweight protection.**

- One-piece lens provides a full and unobstructed field of vision
- Absorb more than 99.9% of harmful UV light
- Molded-in sideshields and browguards
- Adjustable spatula temples
- Package of 12

COMPLIANCE: Meet ANSI Z87.1-2003 standards.

CERTIFICATION: CSA-approved.

Cat. No.	Frame Color	Price
S01822	Black	\$17.25/Pk
S01821	Blue	\$17.25/Pk

fisherbrand Visitorspec Safety Glasses



**Ideal for protecting visitors in
industrial or medical settings.**

Economical safety spectacles available with coated or uncoated lens. Package of 12.

Coated Lens

- 100% impact-resistant lens absorbs more than 99.9% of harmful UV light
- Polycarbonate wraparound style with molded-in browguard and single lens
- Coated to resist scratching, fogging and static
- Adjustable-length spatula temples ensure a secure, comfortable fit

Uncoated Lens

- 100% impact-resistant polycarbonate wraparound unilens design with blue temples
- Clear lens absorbs more than 99.9% of harmful UV light

COMPLIANCE: Meet ANSI Z87.1-2003 standards.

Cat. No.	Frame Color	Lens Type	Price
S01819	Blue	Coated: Scratch-resistant, Anti-fog, Anti-static	\$47.25/Pk
S01820	Blue	Clear, Uncoated	\$29.25/Pk

Eisco™ Clear Safety Glasses, Vented



**Fits over most prescription
lenses and have vents
to prevent fogging.**

- Made of lightweight and durable polycarbonate and impact-resistant lenses with UV protection

COMPLIANCE: CE marked, conforms to ANSI Z87.1 2010 sideshield protection

WARRANTY: 1-year limited manufacturer warranty

Cat. No.	Price
S41140	\$6.80/Ea

Magnifying Safety Glasses with Clip-on, Flip-Up Lens System



**Helps protect the eyes from all sorts of hobbies,
crafts, tasks and other low vision needs.**

- Distortion-free clip-on, flip-up magnifying lenses contain a 1.5X power magnification that is equivalent to +2.5 diopters
- Scratch-resistant polycarbonate lenses and cushioned rubber temple pads for maximum user comfort
- Clear lens design provides UV A/B/C protection along with protective side shields
- Rated for eye protection against low to moderate impact hazards. Glasses are not unbreakable and are not recommended for any high impact hazards (such as but not limited to shooting, racket sports, paintball or any other similar activities)
- Does not provide unlimited protection
- Not rated to protect from hazards including, but not limited to chemical, heat, welding, dust, light (IR/UV/Laser/etc.) and splash hazards
- Must be worn for the whole duration of exposure to hazards, leave the work area if any irritation occurs or if the glasses become damaged or cracked
- Additional protective eyewear such as face shields and helmets should be worn to provide additional protection, depending on the application and the manufacturer's specifications
- Includes a protective PVC storage pouch with a magnetic enclosure system

COMPLIANCE: Meet the ANSI/ISEA Z87.1-2015 personal eye protection standard for impact resistance

WARRANTY: Limited lifetime warranty

Cat. No.	Price
S81167	\$19.25/Ea

Eisco™ Adjustable Clear Safety Goggles, Vented



Designed to protect eyes from chemical splashes and dust.

- Fit over most prescription lens
- Includes side vents to prevent lenses from fogging up
- Features black adjustable strap

COMPLIANCE: ANSI Z87.1 certified

WARRANTY: 1-year limited manufacturer warranty

Cat. No.	Price
S41141	\$9.20/Ea

United Scientific™ Safety Goggles



Manufactured from PVC and are designed to protect against splashes and impact.

- Indirect venting to prevent fogging
- Adjustable strap for a comfortable fit

COMPLIANCE: ANSI Z87.1-2020 Certified

Cat. No.	Price
S111036	\$4.70/Ea

fisherbrand Economy Chemical-Resistant Goggles

Affordable chemical-resistant goggles.

- Clear polycarbonate lens
- Soft, flexible PVC body molds to facial contours for a comfortable fit
- Adjustable headstrap ensures custom fit
- Resist a broad range of chemicals
- Circular vents allow air to flow freely through goggle body



COMPLIANCE: Meets ANSI/ISEA Z87.1-2015 American National Standard for Occupational and Educational Personal Eye and Face Protection Devices, Section 8.1 Droplet and Splash Hazard (D3)

Cat. No.	Price
S68660A	\$4.55/Ea

fisherbrand Chemical Splash Goggles



Lens is coated to minimize scratching and fogging.

- Built for comfortable protection with a soft, flexible PVC body that conforms to facial contours
- Large frames fit over most prescription eyewear
- Coated, clear polycarbonate lens resists impact, scratching and fogging
- Headstrap easily adjusts for a custom fit
- Resist a wide range of chemicals and feature indirect ventilation to direct airflow over the lens

COMPLIANCE: Meet ANSI Z87.1-2003

Cat. No.	Price
S01817	\$6.80/Ea

Eisco™ Green Safety Goggles

General-purpose goggles featuring side vents to prevent fogging.

- With adjustable elastic strap
- Fit over prescription lenses
- Protect from chemical splash and dust

COMPLIANCE: ANSI Z87.1 certified



Cat. No.	Price
S13975	\$2.70/Ea

Visorgogs™ Goggles

Designed to protect eyes from flying particles or liquids.

- Offer complete protection from glaring overhead light
- Lenses are one-piece, impact-resistant plastic with a down-angle vision

COMPLIANCE: Meet ANSI Z87.1-2003 (Z87+ High Impact).



Cat. No.	Price
S47619S	\$9.55/Ea

Eisco™ Adjustable Green Safety Goggles, Indirect Vent

Designed to protect eyes from chemical splash and dust.

- Fit over most prescription lenses
- Indirect vents prevent fogging
- General purpose
- Includes adjustable elastic strap

COMPLIANCE: ANSI Z87.1 certified

WARRANTY: 1-year limited manufacturer warranty



Cat. No.	Price
S88323	\$3.50/Ea

Safety Crews™ Glasses Standard Goggles

Protective goggles with perforated styling for maximum ventilation.

- Made of PVC for comfortable fit over prescription eyewear
- Polycarbonate lens filters 99.9% of harmful UV rays
- Latex-free elastic strap
- Duramass™ scratch-resistant coating



Cat. No.	Price
S14246	\$1.45/Ea

Standard Size Chemical Goggles

Soft vinyl goggle frame conforms to facial contours for a secure fit.

- Fog-free coated lens and four indirect vents minimize fogging
- Fit comfortably over most prescription eyewear
- Fit most adults and high school students

COMPLIANCE: Meet ANSI Z87.1 standards.



Cat. No.	Price
S63095	\$11.25/Ea

Colored Safety Goggles

Can be used any time students need reliable eye protection.

- Sized just right for students and are adjustable for adults
- Set of six pairs of goggles in three bright, translucent colors (red, blue and green)

COMPLIANCE: Meet ANSI Z87.1 safety standards.



Cat. No.	Price
S90821	\$33.00/Pk

Safety Goggles

Durable plastic construction provides good eye protection.

- Flexible body increases wearing comfort
- Great for kids and adults

COMPLIANCE: Meets ANSI Z87.1 standards



Cat. No.	Price
S98484	\$5.95/Ea

Eyewear Cleaning Stations

Keep eyewear clean and clear at all times.

- Perfect for cleaning eyewear (glass or polycarbonate lenses) and computer screens
- Individually wrapped pre-moistened wipes feature anti-fog, anti-static, silicone-free cleaning
- Large 5 x 8 in. wipes are stored in a wall-mounted cardboard dispenser (box of 100)
- Cardboard dispenser dimensions (W x H x D): 4 3/4 x 9 x 2 5/8 in.



Cat. No.	Description	Quantity	Price
S47601	Disposable Station	1 each	\$12.25/Ea
S47631	Pre-moistened Cleaning Wipes	100 wipes	\$12.00/Pk

Diversified Spaces™ Eye Safety Cabinet

The monitor provides excellent protection in five minutes and automatically shuts off if the double doors are opened.

- 24-gauge white enameled steel
- Pilot light confirms UV lamp is in use
- Five-minute cycle controlled by timer
- Doors interlocked with tamper-resistant latches
- Wall and shelf mountable with 7 ft. (2.1 m) grounded electrical cord



Cat. No.	Dimensions (D x W x H)	Price
S02304MF	9.5 x 24.5 x 32 in.	\$2,663.00/Ea

Hand Protection

fisherbrand Powder Free Nitrile Gloves

Provide a superior fit, comfort, tactile sensitivity and dexterity.

- Contains no latex proteins that can cause allergic reactions
- Textured surface for solid grip in wet or dry conditions
- 3.5 mil thick at palm, 4.7 mil at fingertip



Cat. No.	Size	Price
\$79585S	Small	\$19.00/Pk
\$79585M	Medium	\$19.00/Pk
\$79585L	Large	\$19.00/Pk
\$79585XL	X-Large	\$19.00/Pk

fisherbrand Comfort Nitrile Exam Gloves

Powder free and latex-free with a beaded fit and textured fingers.

- Exceptional fit, feel and durability
- Ambidextrous with textured fingers and beaded cuff
- Nonsterile
- Length: 9.5 in. (24 cm)
- Thickness: 3 mil (palm)
- Color: Periwinkle blue



Cat. No.	Size	Price
\$05009A	Small	\$31.50/Pk
\$05009B	Medium	\$31.50/Pk
\$05009C	Large	\$31.50/Pk

Purple Nitrile Gloves

Purple nitrile glove offers maximum protection for higher-risk procedures. Unique color differentiates from latex and other synthetic gloves.

- Textured fingertips provide dexterity and tactile sensitivity
- Latex-free
- Ambidextrous
- 9.5 in. length
- Beaded cuff prevents roll-down and allows for easy donning
- Powder free



Cat. No.	Size	Price
\$78942	X-Small	\$61.50/Pk
\$78943	Small	\$61.50/Pk
\$78944	Medium	\$61.50/Pk
\$78945	Large	\$61.50/Pk
\$78946	X-Large	\$61.50/Pk

Disposable Gloves Zero Waste Box™

Recycle Disposable Gloves. Each box includes signage, a built-in liner, shipping to and from your location, and processing of the materials.

Use this Zero Waste Box to recycle disposable vinyl, nitrile, and latex gloves.

- Do not send in other types of protective gear like hair nets, earplugs, and lab coats or garments. Do not include biodegradable gloves.
- Do not send in medical waste. This includes material contaminated with blood or bodily fluids that originate from healthcare facilities, hospitals, physicians' offices, dental offices, blood banks, veterinary clinics, research laboratories, etc.



How It Works

- Order: Select a Zero Waste Box system and place your order
- Collect: Collect the accepted items to fill the system
- Ship: Send it back to TerraCycle with the prepaid return label on your system
- Reorder: Order your next Zero Waste Box system to continue to recycle everything

What's Included?

- One Zero Waste Box
- One prepaid return label, affixed to your box
- Processing and recycling of the materials

⚠️ ALERTS: Not available in Hawaii, Alaska, and Puerto Rico.

Cat. No.	Capacity (Metric)	Dimensions (L x W x H)	Price
\$88854124	39.66 L	11 x 11 x 20 in.	\$154.00/Ea
\$88854125	79.31 L	11 x 11 x 40 in.	\$290.00/Ea
\$88854126	136.42 L	15 x 15 x 37 in.	\$467.00/Ea

United Scientific™ Silicone Rubber Hand Protector



Constructed of silicone rubber with a specially textured grip for secure handling of hot objects such as beakers, flasks, and bottles.

- Silicone rubber is capable of withstanding high temperatures
- Specially textured grip prevents containers from slipping

Cat. No.	Price
S27814	\$23.50/Ea

Bel-Art™ Hot-Hand™ Silicone Rubber Grip Mitts

Mitts feature concave tipped studs for a non-slip grip, and are capable of withstanding temperatures up to 500°F.

- Protection when handling hot or cold objects, including dry ice
- Capable of withstanding temperatures as high as 260°C (500°F)
- Will remain flexible at temperatures as low as -57°C (-70°F)
- Silicone rubber naturally conforms to hands and objects
- Concave tipped studs provide a non-slip grip
- Easier and faster to use than gloves or tongs for many applications
- One size fits all hands, left or right



Cat. No.	Color	Price
S47371D	Red	\$54.25/Ea
S42988	Blue	\$37.50/Ea
S42989	Green	\$39.25/Ea

Silicone Hand Protector

Silicone Hand Protector for safe handling of hot and cold objects between -70 and 500°F.

- Pockets for thumb and fingers
- Fits every hand size
- Gripping surface studded for positive grip
- Tabs for hanging
- Size: 4 x 7.5 in.
- Sold in cases of 20



Cat. No.	Price
S81046	\$152.00/Cs

Bel-Art™ Clavies™ Heat-Resistant Biohazard Autoclave Gloves

Soft, pliant, cotton terrycloth gloves are ideal for handling hot objects out of the autoclave or oven, and protect from temperatures up to 450°F (232°C).



- Ideal for removing hot objects from an autoclave or oven
- Heat-resistant up to 450°F (232°C)
- Replaces hazardous asbestos gloves
- Extended gauntlet cuff available for additional forearm protection
- Gloves are not waterproof and should not be used to handle dry ice
- Machine wash, air dry, or use the Lab-Aire™ II Glove Holder (03-422-305) to dry on any Lab-Aire™ dryer

Cat. No.	Length (English) Cuff	Price
S47334	5 in.	\$73.75/Pr
S473341	11 in.	\$64.75/Pr

Aprons & Lab Coats

Fisher Scientific™ PVC Aprons

Reusable blue PVC apron with cotton ties at the waist and neck.

Keep a supply of these durable, attractive aprons on hand to protect your body and clothing against accidental spills in the lab or classroom.



Cat. No.	Size	Price
S47381A	Small	\$10.25/Ea
S47382A	Medium	\$11.50/Ea

Fisher Science Education™ PVC Apron of the Elements

Displays current periodic table with properties of 114 elements.

- Reusable
- Blue
- Made of PVC (polyvinyl chloride)
- Cotton ties at the waist and neck



Cat. No.	Size	Price
S32134A	Small	\$10.25/Ea
S32135A	Medium	\$11.25/Ea

How to Choose Respiratory Protection

Protecting What Matters Most

Keeping employees and customers safe is a top priority for all of us, and protecting them from airborne particles and pathogens has never been more important. Use this guide to help choose respiratory protection for you and your colleagues. Find related definitions and distinctions between types of masks and respirators and PPE options based on the operational task.



Disposable Non-Woven Masks

Disposable face masks are designed for single or limited use and are similar to surgical masks in filtration and fluid resistance. Universally sized, they are latex free with soft, elastic ear loops. Not intended for medical use, disposable face masks have 2- or 3-ply construction, do not require fit testing, and are not airtight.

Fisherbrand™ Disposable Face Masks with Ear Loops

Cat. No. 12-888-001A

Available in U.S. and Canada




Procedure and Surgical Masks

Surgical masks are tested to meet levels of barrier protection as specified in ASTM F2100-19. Procedure masks are FDA-approved medical devices for use in healthcare procedures. They do not require fit testing and are not airtight.

Medicom™ SafeMask™ FreeFlow Earloop Mask, Level 3

Cat. No. 19-910-717

Available in U.S. only



N95 Respirators

An N95 mask or respirator filters at least 95% of airborne particles as defined by the U.S. National Institute for Occupational Safety and Health (NIOSH, 42 CFR Part 84). They are functionally equivalent to FFP2 respirators (European Union) and KN95 respirators (China), with slightly different certification criteria.

In the United States, the Occupational Safety and Health Administration (OSHA) requires that healthcare workers use N95 respirators if they are working with patients suspected or confirmed to be infected with COVID-19, Ebola, Mycobacterium tuberculosis, pandemic or avian influenza, or severe acute respiratory syndrome (SARS).

Fit testing is required by OSHA for N95 respirator wearers to both identify the right model, style, and size, and to verify fit thereafter. These respirators can make breathing more difficult, so the wearer must also be medically evaluated for heart conditions, lung disease, and claustrophobia.

Moldex™ N95 Disposable Particulate Respirators

Cat. No. 18-999-1449

Available in U.S. and Canada

Surgical N95 Respirators

Surgical respirators (also called Surgical N95, medical, or healthcare respirators) are N95 masks used specifically in healthcare; they meet both FDA and NIOSH requirements. In response to shortages during the COVID-19 pandemic, the Families First Coronavirus Response Act changed liability and certification requirements to allow the use of industrial N95 respirators.

Fit testing is required by OSHA for N95 respirator wearers to both identify the right model, style, and size, and to verify fit thereafter. These respirators can make breathing more difficult, so the wearer must also be medically evaluated for heart conditions, lung disease, and claustrophobia.

Moldex™ N95 Healthcare Particulate Respirators Surgical Masks

Cat. No. 19-150-0429

Available in U.S. only

Available Resources

- [cdc.gov/coronavirus/2019-ncov/prevent-getting-sick/about-face-coverings.html](https://www.cdc.gov/coronavirus/2019-ncov/prevent-getting-sick/about-face-coverings.html)
- [cdc.gov/niosh/npptl/topics/respirators/disp_part/default.html](https://www.cdc.gov/niosh/npptl/topics/respirators/disp_part/default.html)
- [cdc.gov/niosh/npptl/pdfs/UnderstandDifferenceInfographic-508.pdf](https://www.cdc.gov/niosh/npptl/pdfs/UnderstandDifferenceInfographic-508.pdf)
- [osha.gov/pls/oshaweb/owadisp.show_document?p_id=12716&p_table=standards](https://www.osha.gov/pls/oshaweb/owadisp.show_document?p_id=12716&p_table=standards)
- nelsonlabs.com/en14683-harmonizes-bacterial-filtration-efficiency-and-differential-pressure-with-astm-f2100/
- buyandsell.gc.ca/specifications-for-COVID-19-products#200
- canada.ca/en/health-canada/services/drugs-health-products/covid19-industry/medical-devices/personal-protective-equipment/medical-masks-respirators/face-covering-classifications-notice.html

Useful Links

- [cdc.gov/niosh/npptl/hospresptoolkit/default.html](https://www.cdc.gov/niosh/npptl/hospresptoolkit/default.html)
- [cdc.gov/coronavirus/2019-ncov/communication/print-resources.html](https://www.cdc.gov/coronavirus/2019-ncov/communication/print-resources.html)

ASTM Levels

- **Level 1:** Low barrier protection; for low-risk, non-surgical procedures and exams that do not involve aerosols, sprays, or fluids
- **Level 2:** Moderate barrier protection; for low-to-moderate levels of aerosols, sprays, and fluids
- **Level 3:** Maximum barrier protection; for situations with potential for heavy aerosols, sprays, and fluid exposure

Due to recent unprecedented global demand, some respiratory protection products have limited availability and extended lead times.

Visit fishersci.com/respiratory-protection or fishersci.ca/respiratory-protection to find other respiratory PPE products.

Visit fishersci.com/safety-specialist-contact or fishersci.ca/safety-specialist-contact to contact your safety specialist.



Eye Protection

The Fisher Science Education brand offers a full line of goggles and spectacles that meet OSHA and ANSI standards for eye protection. The information provided below will help you choose the eye protection that is best suited to your application. For additional information and assistance in selecting eye protection, contact Fisher Science Education customer service at **1-800-955-1177**.

OSHA requires that eye and face protective devices meet the ANSI Z87.1 standard for Occupational and Educational Personal Eye and Face Protection Devices.

The ANSI Z87.1 standard sets forth requirements for the testing, marking, selection, care and use of eye protection devices, including spectacles, goggles, and face shields. Rigorous testing including high-mass and high-velocity impact tests are required to verify impact and penetration resistance. ANSI Z87.1 also emphasizes that protective eye devices do not provide complete protection and should not be used as substitutes for protective measures such as mechanical hoods and operational controls.

To comply with OSHA regulations, eye protection equipment must:

- Provide adequate protection against the hazards for which it is designed
- Be marked to identify the manufacturer and that it meets ANSI Z87.1
- Be reasonably comfortable under the conditions of use
- Be durable
- Fit securely without interfering with vision or movement
- Be kept clean and in good repair

Protective Spectacles

Use these glasses for impact protection against flying debris and fragments. Protective spectacles feature plastic, nylon, graphite, or metal frames and removable, vented, or solid sideshields for added protection from particles, such as sand and dirt. All protective spectacles have strong polycarbonate lenses that provide impact resistance and durability, as well as protection from ultraviolet (UV) radiation. Because pits or scratches in lenses may affect impact resistance, lenses should be inspected regularly and replaced if lenses are damaged.

Impact Goggles

These goggles provide more peripheral protection from flying particles than protective spectacles. Perforations in goggle frames provide airflow for comfort and help prevent fogging. Some lenses also feature an antifog coating. Many goggles are designed to fit over prescription eyewear and some will accommodate extra-large eyeglass frames.

Chemical Splash Goggles

Using indirect vents, these goggles protect against splashes of hazardous chemicals or potentially infectious materials. A labyrinth ventilation system rejects contaminants and provides excellent splash protection. Strong polycarbonate lenses provide durability, clarity of vision, and UV protection.

Face Shields

Face shields feature acetate, propionate, or polycarbonate windows for full facial protection against sparks, splashes, and splatter. Polycarbonate windows also provide UV protection, while some specially treated or coated windows offer heat reflection or protection from infrared radiation (IR). Faceshields are secondary protection and must be worn with protective spectacles or goggles.

Eisco™ Clear Vinyl Bib Apron

Clear vinyl bib apron protects clothes during laboratory exercises. Ideal for use in labs, kitchens, or shops.

- Basic transparent vinyl apron
- Perfect for biology, chemistry, and general science laboratories
- Protects clothes from liquid spills and splashes
- Acid resistant



Cat. No.	Size	Price
S27425	X-Small	\$4.55/Ea
S24922	Medium	\$10.00/Ea
S24921	Large	\$7.70/Ea

United Scientific™ Vinyl Apron

Chemical-resistant vinyl fabric that stays flexible.

- Chemical-resistant
- Flexible, vinyl fabric
- Secure cloth ties at the neck and waist
- Reinforced at points of strain



Cat. No.	Size	Price
S27819	Small	\$6.20/Ea
S27820	Medium	\$7.40/Ea
S27821	Large	\$8.35/Ea
S27822	X-Large	\$9.10/Ea

Eisco™ Black Rubber Apron

Extra small size is suitable for children.

- Simple black rubber apron for lab activities, dishwashing, or crafts
- Protects clothes from water and chemical splashes
- Fits around neck, ties in back
- Size: extra small (15 in. width, 22 in. length)
- Suitable for children
- Contains latex



Cat. No.	Size	Price
S27424	X-Small	\$6.50/Ea

Fisher Scientific™ Transparent PVC Aprons

Reusable transparent PVC apron with cotton ties at the waist and neck.

Keep a supply of these durable, attractive aprons on hand to protect your body and clothing against any accidental spills in the lab or classroom.



Cat. No.	Dimensions (L x W)	Price
S475651A	36 x 27 in. (91.4 x 68.6 cm)	\$9.60/Ea
S475652A	42 x 27 in. (106.7 x 68.6 cm)	\$8.25/Ea

Rubberized Chemical Resistant Aprons

Flexible and lightweight.

- Made of chemically-resistant rubberized material
- Reinforced at points of strain
- Ties at waist and neck
- Latex-free
- Color: black



Cat. No.	Length (English)	Width (English)	Price
S475611D	30 in.	24 in.	\$8.30/Ea
S475611A	36 in.	27 in.	\$8.80/Ea
S475611B	42 in.	27 in.	\$11.75/Ea
S475611E	42 in.	36 in.	\$11.75/Ea
S475611C	46 in.	36 in.	\$12.50/Ea

Eisco™ Rubber Laboratory Apron

Chemical-resistant, bib style rubber apron for use in a variety of laboratory settings.

- Comfortable and flexible
- Waterproof
- Resistant to most chemicals
- Contains latex



Cat. No.	Size	Dimensions (L x W)	Price
S24915	Small	30 x 24 in.	\$7.50/Ea
S24916	Medium	36 x 27 in.	\$9.25/Ea
S24914	Large	42 x 27 in.	\$13.75/Ea

Rubberized Cloth Apron

Provides basic protection from chemicals in laboratory or classroom settings.

- Great for laboratory and classroom safety
- Material is rubberized and resistant to most common chemicals
- Cloth tie strings provide steadiness and flexibility



⚠️ ALERTS: Intended for ages 13 and up. May contain latex.

Cat. No.	Dimensions (L x W)	Price
S13707	27 x 36 in.	\$4.25/Ea
S13708	27 x 42 in.	\$4.55/Ea
S13709	36 x 42 in.	\$5.95/Ea
S13710	36 x 46 in.	\$6.50/Ea

United Scientific™ Plastic Disposable Aprons

Protect your staff and students with these disposable plastic aprons.

- This pack of 20 disposable aprons protects clothing from splashes
- Liquid-proof and oil-resistant
- Constructed from 2 mm-thick polyethylene
- One size fits all



Cat. No.	Price
S111125	\$8.40/Pk

Kids Lab Coat

Fine quality kid lab coats for classroom and/or home use. These lab coats are sturdy, moisture absorbent, and ideal for any class or project.

- Knee length
- Two front pockets, one breast pocket
- Side slits for pant pocket access
- Soft and comfortable twill fabric
- Lead and Phthalate free buttons
- Soft and smooth feel, highly sweat-absorbent



Cat. No.	Size	Price
S30777	7	\$15.75/Ea
S30778	8/10	\$15.75/Ea
S30779	12/14	\$15.75/Ea
S30780	16/18	\$14.25/Ea

Eisco™ White Lab Coats

White Lab Coats with long sleeves feature concealed press stud fastenings, backvents, and three large pockets.

- White, modern-style lab coat
- Polyester/cotton twill
- Variety of sizes available

WARRANTY: 1-year limited manufacturer warranty



Cat. No.	Size	Price
S41146	Small	\$25.50/Ea
S41142	Medium	\$25.50/Ea
S41145	Large	\$25.50/Ea
S41147	X-Large	\$25.50/Ea

United Scientific™ Lab Coats

Well-fitted and comfortable.

- Made of easy-care white cotton blend fabric (65% polyester, 35% cotton)
- Knee-length
- One upper left breast pocket and two roomy lower pockets
- With side slit openings and adjustable belt



Cat. No.	Size	Closure Type	Price
S04775	X-Small	Buttons	\$32.75/Ea
S04776	Small	Buttons	\$32.75/Ea
S04777	Medium	Buttons	\$32.75/Ea
S04778	Large	Buttons	\$32.75/Ea
S04779	X-Large	Buttons	\$33.50/Ea
S04780	2X-Large	Buttons	\$40.75/Ea

Unisex Lab Coat

Cool, comfortable and breathable throughout the day.

- Unisex
- 60% cotton, 40% polyester blend - the higher cotton content makes the coat breathable, moisture absorbent, soft and comfortable
- Stays cool throughout the day
- Sizes XS - 5XL
- Full-length (42 inches)
- 3 patch pockets, 2 side access slits, 4 buttons



Cat. No.	Size	Price
S72135	X-Small	\$22.75/Ea
S72136	Small	\$22.75/Ea
S72137	Medium	\$22.75/Ea
S72138	Large	\$22.75/Ea
S72139	X-Large	\$22.75/Ea
S72140	2X-Large	\$24.75/Ea
S72141	3X-Large	\$24.75/Ea
S72142	4X-Large	\$28.50/Ea
S72143	5X-Large	\$28.25/Ea

Facilities

Signage

Electronic Moving Signs with LED

Get maximum visual impact with attention-grabbing messages.




Cat. No.	Dimensions (W x D x H)	Price
19-804-843	49 x 4.25 x 6.25 in.	\$3,940.00/Ea

Hazardous Materials Classification Reference

Hazmat chart is perfect for training or quick reference.

Graphically explains the NFPA hazard identification coding system.



Cat. No.	Dimensions (W x H)	Material	Price
S47352A	10 x 14 in.	Plastic	\$32.00/Ea
S47352D	10 x 14 in.	Vinyl	\$20.50/Ea

Floor Signs with Footprints Symbol

Designed to alert and remind everyone to practice social and physical distancing to prevent the spread of the Coronavirus (COVID-19).

- Constructed of thick adhesive vinyl
- Subsurface printed and laminated to protect the graphics and message from heavy pedestrian traffic
- Non-slip, pebble-textured surface provides added durability
- Strong, permanent, acrylic adhesive back and peel-off liner
- Adheres firmly to smooth, clean, dry surfaces



Cat. No.	Description	Dimensions (L x W)	Price
19-169-620	Footprints Symbol with WAIT HERE	12 x 12 in.	\$32.15/Ea
19-169-621	Footprints Symbol with WAIT HERE	17 x 17 in.	\$47.95/Ea
19-169-624	Footprints Symbol only	12 x 12 in.	\$32.15/Ea
19-169-625	Footprints Symbol only	17 x 17 in.	\$47.95/Ea

Floor Sign – MAINTAIN 6 FT DISTANCE



Designed to alert and remind everyone to practice social and physical distancing to prevent the spread of the Coronavirus (COVID-19).

- Constructed of thick adhesive vinyl
- Subsurface printed and laminated to protect the graphics and message from heavy pedestrian traffic
- Non-slip, pebble-textured surface provides added durability
- Strong, permanent, acrylic adhesive back and peel-off liner
- Adheres firmly to smooth, clean, dry surfaces

Cat. No.	Dimensions (L x W)	Price
19-169-675	3 x 36 in.	\$25.80/Ea

Fold-ups Signs – Multiple Messages

Double-sided signs can be set-up and moved easily to exactly where they are needed.

- Rugged, high-impact plastic construction with handle cut-out
- Fold flat for easy storage and transport
- All signs include the same text and pictogram on both sides
- All signs measure (H x W) 20 x 12 in. (51 x 30.5 cm)



Cat. No.	Message	Color	Price
19-805-086	CAUTION Wet Floor	Black/Red on Yellow	\$138.80/Ea
19-120-2790	Do Not Enter (with international graphic)	Black/Red on White	\$125.50/Ea
19-804-780	CAUTION Tripping Hazard	Black/Red on Yellow	\$125.50/Ea
19-120-2792	Do Not Enter (with hand graphic)	Black/Red on White	\$125.50/Ea

Fire Hose Sign

Safety sign that clearly identifies fire hose location.

- Available in aluminum or plastic
- Color: Red, White
- Language: English



Cat. No.	Dimensions (L x W)	Material	Price
19-169-529	10 x 14 in.	Aluminum	\$41.60/Ea
19-169-528	10 x 14 in.	Plastic	\$23.50/Ea

Safety Signs

Find a range of messages that identify and indicate the potential, type, and degree of hazards that may lead to accidental injury or property damage.

- Durable plastic has slight flex that is ideal for indoor and sheltered outdoor environments
- Printed surface has clear UV protective overcoat
- 50% recycled content with UV inhibitors and good impact resistance
- Rounded corners with 3/16 in. mounting holes for installation
- Comply in accordance with OSHA 29 CFR 1910.145 and ANSI Z535 requirements



Cat. No.	Message	Languages	Dimensions (L x W)	Price
19-169-577	NOTICE EMPLOYEES MUST WASH HANDS BEFORE RETURNING TO WORK	English	7 x 10 in.	\$11.47/Ea
19-169-578	NOTICE EMPLOYEES MUST WASH HANDS BEFORE RETURNING TO WORK	English, Spanish	14 x 10 in.	\$16.57/Ea
19-169-579	CAUTION HAZARDOUS WASTE SATELLITE ACCUMULATION POINT	English	7 x 10 in.	\$11.73/Ea
19-169-580	SATELLITE STORAGE AREA	English	10 x 14 in.	\$17.09/Ea

Projection Sign: Tornado Shelter

Multiple panels provide visibility from numerous angles.

- Hang signs along hallways, stairways, corridors and doorways
- .10 in. thick high-impact plastic
- Images on the two panels are protected by an over-laminate
- Flanged edges have pre-drilled mounting holes
- Wall mount with screw or self-adhesive foam tape (both included)
- 3D signs project 45 degrees from the wall, providing optimum viewing from the front and sides



Cat. No.	Color	Style	Dimensions (H x W)	Price
17-998-122	Black/Blue on Yellow-Glow	3D	6 x 5 in.	\$40.80/Ea
17-998-090	Blue/Black on White	3D	6 x 5 in.	\$34.95/Ea

Safety Projection Sign: Eyewash

Multiple panels provide visibility from numerous angles.

- Hang signs along hallways, stairways, corridors and doorways
- Signs are .10 in. thick high-impact plastic
- Images on the two panels are protected by an over-laminate
- Flanged edges have pre-drilled mounting holes
- Wall mount with screws or self-adhesive foam tape (both included)



Available in two styles:

- **3D signs** project 45 degrees from the wall, providing optimum viewing from the front and sides
- **90° signs** project 90 degrees from the wall and can be viewed from either side

Cat. No.	Color	Shape	Style	Price
17-998-352	Green/White	V-shaped	3D	\$34.45/Ea
17-998-353	Green/White	L-shaped	90°	\$34.20/Ea

Portable Sign Stand

Ideal for temporary applications or crosswalks.

- 6 ft. white powder-coated steel post with pre-drilled mounting holes
- Road-gripping base plate with locking pin
- 40 lb. recycled rubber base



Cat. No.	Price
19-169-611	\$445.00/Ea

Globally Harmonized System Warning Pictogram Poster

Explains the nine Physical, Health and Environmental Hazard pictograms as part of the GHS system of chemicals classification/labeling.


- Heavy glossy paper stock



Cat. No.	Dimensions (L x W)	Price
S08085	24 x 36 in.	\$19.25/Ea

Coronavirus Disease & Prevention Flip Charts

These multimedia kits can help students master key life sciences concepts.



- Colorful laminated charts provide easy-to-follow, illustrated explanations of the coronavirus structure, COVID-19 disease, immunity, vaccines, as well as prevention and protection strategies.
- Each double-sided, 12 x 18 in. chart is laminated and consists of illustrated self-directed readings on one side, with “write-on/wipe off” exercises on the reverse.
- Charts are spiral bound on a sturdy, free-standing easel for easy display anywhere.

CDC Coronavirus Safety Signs in English & Spanish (S81705)

- Set includes the following 5 charts: Symptoms of COVID-19; Managing Your Symptoms; Stop the Spread; Wash Your Hands; and Germs are all Around You
- One side provides illustrated safety information in English, and the reverse side in Spanish

Coronavirus Structure & Immunity Bulletin Board Charts (S81706)

- Set includes the following 4 double-sided, laminated charts: Coronavirus Structure; Coronavirus Cycle: Immune System & Disease; and Therapeutics & Vaccines.
- One side provides an illustrated overview of the topic, while the reverse side features “write-on/wipe-off” related activities

Coronavirus Disease & Prevention Flip Chart Set (S81707)

- Includes the following 10 double-sided, laminated charts: Coronavirus Structure; Coronavirus Cycle; Immune System & Disease; Symptoms of COVID-19; Managing Your Symptoms; How Coronavirus Spreads; How to Protect Yourself & Others; Stop the Spread; Wash Your Hands; and Therapeutics & Vaccines plus a Student Activity Guide with copy-master activities and review questions

Cat. No.	Description	Price
S81705	CDC Coronavirus Safety Signs in English & Spanish	\$36.00/Ea
S81706	Coronavirus Structure & Immunity Bulletin Board Charts	\$29.25/Ea
S81707	Coronavirus Disease & Prevention Flip Chart Set	\$66.50/Ea

Social Distancing Aids

Personal Protection Kit

The kit's PPE provides individual protection from germs, and includes hand and surface disinfectants.



- Protection Kits contain face masks, disposable gloves, hand sanitizer packets, and antimicrobial wipes
- Available for 1 person, or 10 people
- 8 x 10 in. clear bag included

Cat. No.	Type	Includes	Price
12-888-600	1 Person Personal Protection Kit	2 Face Masks, 2 Pairs Disposable Gloves, 2 Hand Sanitizer Packets, 2 Antimicrobial Wipes	\$5.05/Ea
12-888-601	1 Person Personal Protection Kit	2 Face Masks, 3 Pairs Disposable Gloves, 1.75 oz. Hand Sanitizer, 2 Alcohol Wipes	\$21.50/Ea
12-888-602	10 Person Personal Protection Kit	20 Face Masks, 20 Pairs Disposable Gloves, 20 Hand Sanitizer Packets, 20 Antimicrobial Wipes	\$36.75/Ea

FeatherLite™ Panels

Stay protected with this convenient, easy setup panel.

Clean with soap and water or antibacterial sprays.



Cat. No.	Material	Dimensions (W x D x H)	Price
S81589	Vinyl	57 x 24 x 70 in.	\$228.00/Ea
S81590	Vinyl	57 x 24 x 52.5 in.	\$205.00/Ea
S81591	Vinyl	57 x 24 x 35 in.	\$185.00/Ea
S81592	Acrylic	57 x 24 x 70 in.	\$546.00/Ea
S81593	Acrylic	57 x 24 52.5 in.	\$399.00/Ea
S81594	Acrylic	57 x 24 x 35 in.	\$319.00/Ea

Sneeze-Guard, Edge Mounted

Stay protected with this convenient, easy setup panel.

Clean with soap and water or antibacterial sprays.



Cat. No.	Dimensions (H x W)	Price
S81606	18 x 30 in.	\$76.00/Ea
S81607	24 x 30 in.	\$94.00/Ea
S81604	18 x 24 in.	\$56.75/Ea
S81605	24 x 24 in.	\$68.00/Ea

Sneeze-Guard, Upright Mounted

Stay protected with this convenient, easy setup panel.

Clean with soap and water or antibacterial sprays.



Cat. No.	Dimensions (H x W)	Price
S81595	14 x 48 in.	\$77.00/Ea
S81598	14 x 60 in.	\$144.00/Ea
S81601	14 x 72 in.	\$209.00/Ea
S81596	26 x 48 in.	\$97.00/Ea
S81599	26 x 60 in.	\$180.00/Ea
S81602	26 x 72 in.	\$260.00/Ea
S81597	38 x 48 in.	\$117.00/Ea
S81600	38 x 60 in.	\$214.00/Ea
S81603	38 x 72 in.	\$311.00/Ea

Free Standing Sneeze Guard

Stay protected with this convenient, easy setup panel.

Clean with soap and water or antibacterial sprays.



Cat. No.	Dimensions (H x L)	Price
S81576	24 x 24 in.	\$72.00/Ea
S81578	24 x 30 in.	\$85.00/Ea
S81580	24 x 48 in.	\$175.00/Ea
S81579	38 x 30 in.	\$179.00/Ea
S81577	40 x 24 in.	\$127.00/Ea

Free Standing Sneeze Guard with Pass Through

Stay protected with this convenient, easy setup panel.

Clean with soap and water or antibacterial sprays.




Cat. No.	Dimensions (H x L)	Price
S81581	24 x 18 in.	\$58.25/Ea
S81582	24 x 24 in.	\$74.50/Ea
S81584	24 x 30 in.	\$84.00/Ea
S81586	24 x 48 in.	\$175.00/Ea
S81585	38 x 30 in.	\$172.00/Ea
S81583	40 x 24 in.	\$124.00/Ea

Ceiling Sneeze Guard

Stay protected with this convenient, easy setup panel.

Clean with soap and water or antibacterial sprays.



Cat. No.	Dimensions (H x L)	Price
S81587	24 x 24 in.	\$71.00/Ea
S81588	48 x 24 in.	\$177.00/Ea

Cleaners and Sanitizers

Hand Sanitizer Gel and Pump

Gel formula hand sanitizer (70% ethyl alcohol) with aloe and vitamin E.

- Kills germs and protects your hands
- Made in the U.S.A. according to FDA guidelines
- Independently tested and verified by a third party lab



Cat. No.	Size (English)	Price
12-888-608	8 oz.	\$8.40/Ea

Diversified Spaces™ Hand Sanitizer Unit (Stand & Dispenser)

A complete hand sanitizer unit with stand and dispenser. The stand is suitable for indoor and outdoor use, with a durable powder-coated base and mounting plate to withstand the elements. The dispenser mounts on the stand with an universal mounting plate.

- Dispenser includes a refillable plastic bottle (1,000 mL capacity)
- Easy to assemble
- Heavyweight, free-standing design
- Indoor/outdoor Stand and dispenser
- Powder-coated base
- Requires 4 x C batteries (not included)
- Stands 49.5 in. tall when assembled
- Touchless, motion-activated gel dispenser
- Universal mounting plate with theft-resistant screws or double-sided tape (not included)



Cat. No.	Price
S81425	\$137.00/Ea

Diversified Spaces™ Hand Sanitizer Dispenser

A motion-activated, touchless gel dispenser that provides clean, accessible hand sanitization.

- 1,000 mL refillable plastic bottle included
- Hand sanitizer gel is not included
- Hands-free, touchless, motion activated design
- Requires 4 x C batteries
- Universal gel dispenser
- Works with standard hand sanitizer gels



Cat. No.	Price
S81427	\$59.75/Ea

Diversified Spaces™ Hand Sanitizer Stand

Suitable for indoor and outdoor use, with a durable powder-coated base and mounting plate to withstand the elements.

- Easy to assemble
- Heavyweight, free-standing design
- Indoor/outdoor stand
- Powder-coated base
- Stand includes a universal mounting plate with theft-resistant screws or double-sided tape (not included)



Cat. No.	Price
S81426	\$79.00/Ea

Eisco™ Goggle Sanitizing Cabinet

UV light kills the germs on goggles after use.

- Wall-mounted or bench top unit runs on 120 VAC
- Heavy gauge CRC steel treated with white enamel finish
- Unit has doors and includes a 15 minute timer with UV bulb
- UV light operates only when doors are closed
- Light leak avoided by tight fitting piano style hinges
- Sterilization process is indicated by indicator light
- Use to sanitize 36 pairs



Cat. No.	Description	Size	Price
S07817	Goggle Sanitizing Cabinet	26 x 10 x 29 in. (66 x 25.4 x 73.7 cm)	\$832.00/Ea
S24853	Germicidal Replacement Bulb	Philips T8 TUV fluorescent bulb	\$76.00/Ea

UV Sanitizer Cabinets

These UV sanitizer cabinets are designed for the disinfection of small tools and objects. Useful in killing germs, bacteria, viruses and fungi.



Both units feature

- 30-minute timer
- A safety feature prevents UV light from operating unless doors are properly closed and latched



S81792 small, desktop cabinet features

- Two removable, easy to clean stainless steel shelves

S81791 bench top or wall mount cabinet features

- Cabinet is made of heavy gauge steel with enamel finish
- Designed to prevent any UV ray leakage during operation
- Comes with a filtered viewing lens hole for checking operations while in use
- Six removable 202-grade stainless steel shelves
- Input voltage: 110 to 220 V AC ±10%, 50/60 Hz

COMPLIANCE: All components are UL approved

Cat. No.	Size (L x H x D)	Lamp	Weight	Price
S81792	20.50 x 16 x 16 in.	Two built-in 254 nm UV lamps	31 lb.	\$479.00/Ea
S81791	26 x 29 x 10 in.	High power 25 W UVC lamp	53 lb.	\$709.00/Ea

Economy Ultraviolet Goggle Sanitizers

Sanitize and store 30 to 40 goggles or safety glasses in the same cabinet.

- High-quality, 24-gauge, white baked enamel sheet metal
- 15-minute mechanical timer ensures controlled treatment
- Two safety door switches, key lock and pilot light
- Long-life ultraviolet bulbs



Cat. No.	Description	Height	Device Holds	Price
S47604A	Goggle Sanitizer	26 in.	30 pairs of goggles	\$753.00/Ea
S47604BLB	Replacement bulb			\$51.50/Ea

Sinks and Eyewash Stations

Diversified Spaces™ Stainless Steel Mobile Sinks

Mobile stainless-steel sink allows personnel to wash their hands in the absence of fixed plumbing.

- Easy to refill fresh water – no disassembly needed
- 115 volt 3.3 GPM, 45 PSI water diaphragm pressure pump (CSA Listed)
- 15 ft. GFCI power cord with standard wall plug (UL Listed)
- 18 gauge stainless steel body
- 4 gauge stainless steel top
- 5 gallon removable fresh water tank
- 7 gallon removable waste water tank
- Drain hose for easy draining
- Four locking 5 in. casters for easy mobility (2 swivel, 2 locking)
- Heavy duty stainless steel construction
- Hose connections
- Lockable access door
- Sink size: 10 x 14 x 5 in.
- Soap & towel dispenser



Cat. No.	Description	Price
S81500	Stainless Steel Sensor Faucet Cold Water Sink	\$8,301.00/Ea
S81501	Stainless Steel Sensor Faucet Hot Water Sink	\$9,972.00/Ea
S81498	Stainless Steel Metered Cold Water Sink	\$7,967.00/Ea
S81499	Stainless Steel Metered Hot Water Sink	\$8,891.00/Ea

Diversified Spaces™ Shower/Eyewash Station

Provides convenient storage for lab safety supplies.

- Emergency drench shower head
- High-impact ABS plastic
- Chemical-resistant earth-friendly UV finish
- Stay open chrome-plated brass valve
- Eyewash unit: stainless steel bowl (diameter: 10 in.,)
- Lever action ball valve on plastic laminate top
- Two adjustable shelves

CERTIFICATION: SEFA, MAS Certified Green



Cat. No.	Product Type	Price
S38038	Shower station	\$3,684.00/Ea
S38039	Shower station with locks (for security or access for a wheelchair)	\$4,043.00/Ea

Faucet-Mount Eyewashes

Eyewashes attach easily to any standard laboratory faucet; no special plumbing needed.

- Made of chrome-plated brass with float-off dust covers
- Back-mount unit provides 1.5 gpm
- Angled unit has flow control

COMPLIANCE: Meet ANSI Z358.1-1998 standards

⚠️ ALERTS: To avoid scalding, cold water or tempered water connection is recommended



Cat. No.	Price
S47621	\$293.50/Ea

Safety Cans

Bel-Art™ Benchtop Biohazard Disposal Can with Motion Sensor Lid

Compact benchtop biohazard disposal controls odors and is perfect for small items like pipette tips and microcentrifuge tubes.

- Automatic opening lid provides hands-free use; closes automatically and securely for a more sanitary environment
- Holds a 25 x 25 cm (10 x 10 in.) autoclavable biohazard disposal bag (S43506)
- Includes a polypropylene liner with handle for easy emptying of contents
- Aesthetic and durable; stainless steel body and chrome lid are resistant to bleach and easy to clean
- Requires 3 AAA batteries (not included)
- Compliance: CE & RoHS



Cat. No.	Price
S72309	\$69.25/Ea

Nonmetallic Oval Type I Safety Cans For Flammables



30% more storage capacity than round shape models.

- Constructed of high-density polyethylene
- Trigger mechanism enables pouring of small quantities of liquid
- Leak-tight, self-closing cap prevents spillage and automatically vents to guard against explosion
- Dual-density flame arrester protects against external heat sources
- Current-carrying carbon insert is embedded into can for proper grounding
- Nonmetallic, stainless steel hardware



Cat. No.	Capacity	Price
S04768MF	1 Gallon	\$131.50/Ea
S04769MF	1/2 Gallon	\$120.00/Ea

Safety Cans

A safe way to carry and store flammable liquids.

- Constructed of galvanized steel with a brass pour spout
- Single-walled, brass flame arrestor is located within the pour spout
- Store acetone, toluene, xylene, naphtha, gasoline, and other noncorrosive flammable liquids

COMPLIANCE: UL listed; FM approved



Cat. No.	Capacity	Price
S41789	1 Gallon	\$76.75/Ea

Eisco™ Laboratory Safety Chart

Laboratory safety chart with colored illustrations can be used in any school laboratory.

- Printed on 29 x 39 in. polyart plastic sheet fitted with plastic roller
- Communicates vital safety information
- Ideal for school laboratories



Cat. No.	Price
S26685	\$32.00/Ea

Universal Mini Chemical Spill Kit

Be prepared for spills in your lab. Universal sorbent eliminates guesswork and is safe for use on all chemicals except hydrofluoric acid.



Kit includes:

- Enough material to absorb 1 L of solvent
- 1 kg universal sorbent
- 1 pair nitrile gloves
- 1 pair splash-resistant goggles
- 1 dustpan and brush set
- 2 poly bags 9 x 16
- 2 twist ties
- 2 blank tags
- Instruction sheets
- SDS

Cat. No.	Price
S28619***	\$33.25/Ea

Acid, Caustic and Solvent Combination Spill Kit



Kit contains enough material to clean up one liter of four solvents.

Kit Includes:

- 1100 g diatomaceous earth (flammable absorbent material)
- 1.0 kg acid spill cleanup kit (acid neutralizing mixture)
- 1.2 kg spill kit, caustic cleanup (caustic neutralizing mixture)
- 200 g vermiculite (absorbent)
- Splash-resistant goggles
- 24 nitrile gloves
- 1 dustpan and brush set
- 1 spill kit storage container

Cat. No.	Price
S20636***	\$172.00/Ea



FEATURED SUPPLIERS
MORE FOR YOU

Visit fisheredu.com/featuredsuppliers to learn more about enhanced products and promotional information.

Safety Equipment and Protective Gear Zero Waste Box™

Recycle safety equipment and protective gear. Each box includes signage, a built-in liner, shipping to and from your location, and processing of the materials.

Use this Zero Waste Box to recycle disposable safety equipment and protective gear.

- This includes all brands and sizes of ear plugs, beard nets, hair nets, gloves, safety glasses, disposable garments, and masks.
- Do not send in medical waste: material contaminated with blood or bodily fluids that originate from healthcare facilities, hospitals, physicians' offices, dental offices, blood banks, veterinary clinics, research laboratories, etc.

How It Works

- Order: Select a Zero Waste Box system and place your order
- Collect: Collect the accepted items to fill the system
- Ship: Send it back to TerraCycle with the prepaid return label on your system
- Reorder: Order your next Zero Waste Box system to continue to recycle everything

What's Included?

- One Zero Waste Box
- One prepaid return label, affixed to your box
- Processing and recycling of the materials

⚠️ ALERTS: Not available in Hawaii, Alaska, and Puerto Rico.

Cat. No.	Dimensions (L x W x H)	Capacity (Metric)	Price
S475652	11 x 11 x 20 in.	39.66 L	\$178.00/Ea
S475653	11 x 11 x 40 in.	79.31 L	\$341.00/Ea
S475654	15 x 15 x 37 in.	136.42 L	\$559.00/Ea



Storage Cabinets

Safety Cabinet With Handles, For Flammables

Non-slip gripper allows fingertip opening.

- Flush-mounted door handle with two keys for security
- Handle can be padlocked (padlock not included), no interference with traffic
- Exclusive self-latching feature ensures safe closing of cabinet doors without manually engaging door handle, ensuring fire protection
- Double-wall construction provides 1.5 in. (3.8 cm) of insulating air space to help prevent spread of flames
- High-visibility Haz-Alert™ reflective warning labels offer added safety during power outages or fires
- Dual vents with flame arresters at top and opposite bottom allow hazardous vapors to be piped away
- Two-door models hinged left and right with self-closing mechanism ensures proper closing sequence
- Fusible links hold self-closing doors wide open, flush with front of cabinet for easy access and resupply; automatically release and slam doors shut at 165°F (74°C)
- Concealed self-close mechanism provides optimum storage space and obstruction-free access to contents
- SpillSlope™ safety shelves direct incidental spills to the back and bottom of leakproof sump
- Adjustable leveling feet ensure solid positioning and alignment for tight door closure
- Exterior side panel has built-in grounding connector for easy grounding
- Finished inside and out with durable lead-free powder paint
- Meet OSHA and NFPA requirements
- Color: Yellow

COMPLIANCE: Meet NFPA Code 30 and OSHA regulations; models with self-close doors also comply with the International Fire Code and NFPA1, FIRE CODE.

CERTIFICATION: FM-approved

WARRANTY: 10 years

Cat. No.	Load Bearing Capacity	Door Style	No. of Doors	Price
S04761MF	45 gal.	Manual-close	2	\$1,951.00/Ea
S04763MF	45 gal.	Self-closing	2	\$2,303.00/Ea
S04762MF	45 gal.	Self-closing	1	\$3,571.00/Ea
S04760MF	30 gal.	Manual-close	2	\$1,491.00/Ea



Flammable Safety Cabinet

Reduce fire risks, improve productivity by storing flammable fuels and chemicals in code-compliant safety cabinets.



- Self-latch engages critical three-point latching system for protection under fire conditions
- Double-wall 18-gauge welded steel construction provides 1.5 in. (3.8 cm) of insulating air space for fire resistance
- Manual-close door opens to full 180 degrees and self-latches when pushed closed
- Self-close door shuts and latches automatically when fusible link melts at 165°F (74°C) under fire conditions
- Unique, concealed self-closing mechanism offers obstruction-free access to contents
- Durable lead-free epoxy/polyester powder-coat finish provides chemical resistance
- Features dual vents with flame arresters, four adjustable self-leveling feet, grounding connector, and trilingual warning label
- For added security, U-Loc™ handle comes with cylinder lock and key set or accepts optional padlock
- Haz-Alert™ reflective warning labels are highly visible under fire conditions or during power outages when illuminated with flashlight
- SpillSlope™ safety shelves direct incidental spills to back and bottom of leakproof sump



COMPLIANCE: Meets OSHA and NFPA 30 regulations; self-close door styles also meet NFPA 1 and International Fire Code.

CERTIFICATION: FM approved

WARRANTY: 10 years

Cat. No.	Door Style	Interior Dimensions (D x W x H)	Price
S15223MF	Manual-close	30.3 x 30.7 x 60.5 in.	\$2,290.00/Ea
S15224MF	Self-close	30.3 x 30.7 x 60.5 in.	\$2,845.00/Ea

Flammables Cabinets

Includes four adjustable leveling feet.

- Top and bottom vents are fitted with 2 in. (5 cm) pipe thread on sidewalls
- Double walls of 18-gauge steel provide 1.5 in. (3.8 cm) air space
- 2 in. (5 cm) raised sill contains spills
- Adjustable galvanized steel shelves supported by four brackets hold over 500 lb. (227 kg) each
- Self-closing doors have fusible link that melts at 71°C (160°F)
- Three-point key lock
- Labeled "FLAMMABLE — KEEP FIRE AWAY"



COMPLIANCE: FM approved, except S51021MF; meets OSHA and NFPA Code 30 requirements

Cat. No.	Load Bearing Capacity	Door Style	No. of Doors	Price
S51021MF	45 gal.	Self-close	2	\$2,194.00/Ea

Flammables Safety Can Storage Cabinets With Handles

Keep dangerous liquids safely organized and segregated. Cabinets feature flush mounted handles, two keys for security and have the ability to be padlocked. Dual vents with flame arresters allow hazardous vapors to be piped away.



- Flush-mounted door handle does not interfere with traffic; comes with two keys for security and can be padlocked (padlock not included)
- Exclusive self-latching feature ensures that cabinet doors are safely closed without manually engaging door handle
- Double-wall construction provides 1.5 in. (3.8 cm) of insulating air space to help prevent spread of flames
- High-visibility Haz-Alert™ reflective warning labels offer added safety during power outages or fires
- Dual vents with flame arresters at top and opposite bottom allow hazardous vapors to be piped away
- Easy-closing, self-latching doors facilitate fire protection of the cabinet
- Self-latch engages critical three-point latching system for protection under fire conditions
- Fusible links hold self-closing doors wide open, flush with front of cabinet for easy access and resupply; automatically release and slam doors shut at 74°C (165°F)
- Concealed self-close mechanism provides optimum storage space and obstruction-free access to contents
- Two-door models hinged left and right have self-closing mechanism that ensures proper closing sequence regardless of which door is released first
- SpillSlope™ safety shelves direct incidental spills to the back and bottom of leakproof sump
- Adjustable leveling feet ensure solid positioning and alignment for tight door closure
- Exterior side panel has built-in grounding connector for easy grounding
- Finished inside and out with durable lead-free powder paint
- Meet OSHA and NFPA requirements

COMPLIANCE: FM, NFPA, OSHA, U (NFPA)

Cat. No.	Interior Dimensions (D x W x H)	No. of Shelves	Price
S28708	14.56 x 39.5 x 39.62 in.	1	\$1,762.00/Ea
S28749	30.34 x 39.5 x 60.5 in.	2	\$2,845.00/Ea
S28750	30.34 x 39.5 x 60.5 in.	2	\$3,387.00/Ea

Acid Cabinets

Polypropylene lock assembly, padlock with two keys.

- Constructed of 1 in. (2.5 cm) thick plywood with acid-resistant epoxy paint
- Wooden dowel hinge assembly eliminates the problem of hinge deterioration
- Single fixed shelf is positioned for storage of large 4 L bottles on top shelf and 2.5 L bottles on bottom shelf
- Recessed top with polypropylene tray holds 12 L of spilled liquid
- Floor includes 2 in. (5.1 cm) liquid-tight trough
- Storage capacity: thirty 2.5 L or ninety 500 mL bottles
- Partially lined model has polypropylene on the floor, shelf and top tray
- Fully lined model has polypropylene on the floor, interior walls, interior top, and top tray



Cat. No.	Product Type	Price
S51073MF	Fully-lined acid cabinet	\$2,968.00/Ea
S51072MF	Partially-lined acid cabinet	\$2,310.00/Ea

Blue Steel Safety Cabinets for Corrosives

Epoxy baked-on powder coat finish provides increased chemical resistance, and resists solvents used in labs.

- Double-wall construction and dual vents
- Grounding wire connections and leakproof sills
- Three-point self-latching doors and leveling feet
- Available in different capacities and varying numbers of adjustable shelves
- Polyethylene trays are attached to galvanized steel shelves and separate polyethylene liner for bottom sump
- Extra polyethylene top work tray in 30 gal. (15 L) two-door cabinet



Cat. No.	Load Bearing Capacity	No. of Doors	No. of Shelves	Price
S04767MF	45 gal. (170 L)	2	2	\$2,479.00/Ea
S04766MF	30 gal. (113.5 L)	1	1	\$3,143.00/Ea

Polyethylene Corrosives/Acid Cabinet

Sturdy, completely metal-free poly cabinet for storing acids or bases without the worry of corrosion.

- Holds up to 36, 2.5 L bottles
- Offers chemical resistance against spills or potential damaging vapors when storing acids or bases
- Removable yet sturdy sump cover, that also serves as a bottom shelf, and conceals the fully integrated, leakproof sump with an 8.5 gal (32 L) capacity
- Recessed channels in shelf and base help direct spills to the back of the cabinet and down into the sump
- Three application-specific labels identify contents to safely store and segregate incompatible chemicals — ACID, BASE, and CORROSIVE
- Cabinet can be used for stand-alone storage
- Doors open nearly 180 degrees for easy access, engage firmly with the body



when closed, and accept a padlock (not included)

- Grooved top work surface
- Recessed toe-kick allows the user to stand closer to the counter for improved ergonomics
- Two cabinets can be stacked—top cabinet offers convenient eye-level access to contents
- Four pre-formed vent locations at rear provide a guide for an aftermarket vent kit (not included) in the event the application requires a pressurized vapor removal system
- Shelf adjusts on 3-in. (76 mm) increments, and has a load capacity of 125 lb. (57 kg)

⚠️ ALERTS: Research environments using many different types of chemicals have special storage requirements. Whether using acids, bases or solvents, it is critical that incompatible liquids are segregated to avoid disastrous explosions or fire. The SDS (Safety Data Sheet) should be reviewed to determine chemical characteristics and recommended storage practices.

Cat. No.	Dimensions (D x W x H)	Price
S27960MF	Exterior: 36 x 35 x 25 in. Interior: 31.25 x 28 x 18 in.	\$2,163.00/Ea

Wood Laminate Storage Cabinets for Corrosives and Acids

Suitable for storing highly corrosive liquids such as phenol, nitric acid and sulfuric acid.

- Long-lasting wood construction provides exceptional strength
- Stainless steel handles and hinges resist corrosion from harsh acids
- Shelves adjust on 32 mm centers to accommodate a wide variety of containers
- Sturdy clip system adjusts shelves if required
- Ideal for smaller quantities used at workbench level
- No shelves
- Two doors
- Color: blue



Cat. No.	Load Bearing Capacity	Dimensions (D x W x H) Interior	Price
S04764MF	6 x 2.5 L bottles	15.28 x 22.48 x 19.44 in. (38.8 x 57.1 x 49.4 cm)	\$1,148.00/Ea

Bel-Art

Biohazard Disposal Can	28
Fire Blanket	6
Gloves, Autoclave.....	17
Silicone Rubber Grip Mitts.....	17

Diversified Spaces

Eyewear Safety Cabinet.....	15
Hand Sanitizer Stand & Dispensers.....	26–27
Shower/Eyewash Station.....	28
Sinks, Stainless Steel Mobile.....	28

Eisco

Aprons	21
Face Masks, Disposable.....	12
Face Shields	12
Goggles.....	14–15
Goggle Sanitizing Cabinet.....	27
Lab Coats.....	22
Laboratory Safety Chart	29
Safety Glasses.....	13
Safety Shields.....	12

Fisherbrand

Bandages, Flexible	7
Dry Bath Blocks	4
Face Masks, Disposable.....	18
Face Shields	12
Gloves.....	5, 16
Goggles.....	14
Safety Glasses.....	13

Fisher Science Education

Aprons	17
--------------	----

Fisher Scientific

Aprons	17, 21
--------------	--------

Thermo Scientific

Dry Baths	4
Hotplates and Stirrers	4
Vortex Mixers.....	4
Water Baths.....	4

United Scientific

Aprons	21–22
Biohazard Disposable Bags	5
Goggles.....	14
Hand Protector, Silicone Rubber	17
Lab Coats.....	22

Alphabetical Index

A	
Adhesive Bandages	7
Alcohol Swabs	7
Aprons	5, 17, 21–22
B	
Bandages	7
Biohazard Disposal	
Bags	5
Cans	28
Bleeding Control Kits	8–9
C	
Cans	
Biohazard Disposal	28
Flammable Storage	29
Coronavirus Education	25
Coronavirus Safety Signs	25
D	
Defibrillators	6–7
Electrodes	7
Disposable Face Masks	12, 18
Disposal Boxes	
Gloves	16
Masks	12
Safety Equipment and Protective Gear	30
E	
Emergency Incident Command Station	9
Emergency Kits	8–11
Eye Protection	5, 12–15, 20
Eyewash Stations	28
Eyewear	5, 12–15, 20
F	
Face Masks	12, 18, 25
Face Shields	12, 20
Fire Blanket	6
First Aid	6–11
Alcohol Swabs	7
Backpack Kits	9
Bandages	7
Defibrillators	6–7
Evacuation Chairs	6
Fire Blanket	6
Scissors	7
Trauma Kits	8–11
G	
Gloves	
Autoclave	17
Exam	5, 16
Nitrile	5, 16
Goggles	5, 14–15, 20
Goggle Sanitizing Cabinets	15, 27

H	
Hand Protection	16–17
Hand Protector, Silicone Rubber	17
Hand Sanitizers & Dispensers	25–27
Hotplates and Stirrers	4
L	
Lab Coats	22
Laboratory Safety Chart	29
Lockdown Kits	10–11
M	
Masks	12, 18–19, 25
N95	11, 19
Mitts, Grip	17
Mixer	4
N	
N95 Respirators	11, 19
P	
Panels, Sneeze Guard	25–26
Personal Protection Kit	25
R	
Respirators	
N95	11, 19
S	
Safety Glasses	13–15, 20
Sanitizer Cabinets	15, 27
Scissors, Bandage	7
Shelter-In-Place Emergency Kits	10–11
Shower/Eyewash Station	28
Signage	23–25
Silicone Rubber Grip Mitts	17
Sinks, Mobile	28
Social Distancing Aids	25–26
Stirring Hotplate	4
Swabs, Alcohol	7
V	
Vortex Mixer	4
W	
Waste Disposal	5, 12, 16, 30
Water Baths	4
Wipes	15, 25

Lined area for taking notes.

Unless otherwise expressly agreed in writing, all sales are subject to the following terms and conditions:

GENERAL: Fisher Scientific Company L.L.C. ("Seller") hereby offers for sale to the buyer named in the order ("Buyer") the products listed on the face hereof (the "Products") on the express condition that Buyer agrees to accept and be bound by the terms and conditions set forth herein. Any provisions contained in any document issued by Buyer are expressly rejected and if the terms and conditions in this Agreement differ from the terms of Buyer's offer, this document shall be construed as a counter offer and shall not be effective as an acceptance of Buyer's document. Buyer's receipt of Products or Seller's commencement of the services provided hereunder will constitute Buyer's acceptance of this Agreement. This is the complete and exclusive statement of the contract between Seller and Buyer with respect to Buyer's purchase of the Products. No waiver, consent, modification, amendment or change of the terms contained herein shall be binding on Seller unless in writing and signed by Seller and Buyer. Notwithstanding the foregoing, Seller reserves the right to make changes to these Terms and Conditions of Sale at any time by posting such changes here, and such changes shall apply to orders of Products made by Buyer thereafter. Seller's failure to object to terms contained in any subsequent communication from Buyer will not be a waiver or modification of the terms set forth herein. All orders are subject to acceptance in writing by an authorized representative of Seller. Seller reserves the right to reject any order for any reason. By purchasing products from Seller, Buyer agrees that it is purchasing the Products only for its own use and not for purposes of resale. Products purchased pursuant to these Terms and Conditions may not be sold or transferred to any person or entity for purposes of resale. Seller reserves the right to take any action it deems necessary to address Buyer's violation of these terms, including, but not limited to, the suspension of Buyer's ability to purchase Products.

PRICE: All prices published by Seller or quoted by Seller's representatives may be changed at any time without notice. All prices quoted by Seller or Seller's representatives are valid for thirty (30) days, unless otherwise stated in writing. All prices for the Products will be as specified by Seller or, if no price has been specified or quoted, will be Seller's price in effect at the time of shipment. All prices are subject to adjustment on account of specifications, quantities, raw materials, cost of production, shipment arrangements or other terms or conditions which are not part of Seller's original price quotation. List prices may vary from the price displayed on the website for certain products.

TAXES AND OTHER CHARGES: Prices for the Products exclude all sales, value added and other taxes and duties imposed with respect to the sale, delivery, or use of any Products covered hereby, all of which taxes and duties must be paid by Buyer. If Buyer claims any exemption, Buyer must provide a valid, signed certificate or letter of exemption for each respective jurisdiction.

TERMS OF PAYMENT: Seller may invoice Buyer upon shipment for the price and all other charges payable by Buyer in accordance with the terms on the face hereof. If no payment terms are stated on the face hereof, payment shall be net thirty (30) days from the date of invoice. If Buyer fails to pay any amounts when due, Buyer shall pay Seller interest thereon at a periodic rate of one and one-half percent (1.5%) per month (or, if lower, the highest rate permitted by law), together with all costs and expenses (including without limitation reasonable attorneys' fees and disbursements and court costs) incurred by Seller in collecting such overdue amounts or otherwise enforcing Seller's rights hereunder. Seller reserves the right to require from Buyer full or partial payment in advance, or other security that is satisfactory to Seller, at any time that Seller believes in good faith that Buyer's financial condition does not justify the terms of payment specified. All payments shall be made in U.S. Dollars.

DELIVERY; CANCELLATION OR CHANGES BY BUYER: The Products will be shipped to the destination specified by Buyer, F.O.B. Seller's shipping point. Seller will have the right, at its election, to make partial shipments of the Products and to invoice each shipment separately. Seller reserves the right to stop delivery of Products in transit and to withhold shipments in whole or in part if Buyer fails to make any payment to Seller when due or otherwise fails to perform its obligations hereunder. All shipping dates are approximate only, and Seller will not be liable for any loss or damage resulting from any delay in delivery or failure to deliver which is due to any cause beyond Seller's

reasonable control. In the event of a delay due to any cause beyond Seller's reasonable control, Seller reserves the right to terminate the order or to reschedule the shipment within a reasonable period of time, and Buyer will not be entitled to refuse delivery or otherwise be relieved of any obligations as the result of such delay. Products as to which delivery is delayed due to any cause within Buyer's control may be placed in storage by Seller at Buyer's risk and expense and for Buyer's account. Orders in process may be canceled by Buyer only with Seller's written consent and upon payment of Seller's cancellation charges. Orders in process may not be changed by Buyer except with Seller's written consent and upon agreement by the parties as to an appropriate adjustment in the purchase price therefore. Credit will not be allowed for Products returned without the prior written consent of Seller.

TITLE AND RISK OF LOSS: Notwithstanding the trade terms indicated above and subject to Seller's right to stop delivery of Products in transit, title to and risk of loss of the Products will pass to Buyer upon delivery of possession of the Products by Seller to the carrier; provided, however, that title to any software incorporated within or forming a part of the Products shall at all times remain with Seller or the licensor(s) thereof, as the case may be.

WARRANTY: Seller warrants that the Products will operate or perform substantially in conformance with Seller's published specifications and be free from defects in material and workmanship, when subjected to normal, proper and intended usage by properly trained personnel, for the period of time set forth in the product documentation, published specifications or package inserts. If a period of time is not specified in Seller's product documentation, published specifications or package inserts, the warranty period shall be one (1) year from the date of shipment to Buyer for equipment and ninety (90) days for all other products (the "Warranty Period"). Seller agrees during the Warranty Period, to repair or replace, at Seller's option, defective Products so as to cause the same to operate in substantial conformance with said published specifications; provided that Buyer shall (a) promptly notify Seller in writing upon the discovery of any defect, which notice shall include the product model and serial number (if applicable) and details of the warranty claim; and (b) after Seller's review, Seller will provide Buyer with service data and/or a Return Material Authorization ("RMA"), which may include biohazard decontamination procedures and other product-specific handling instructions, then, if applicable, Buyer may return the defective Products to Seller with all costs prepaid by Buyer. Replacement parts may be new or refurbished, at the election of Seller. All replaced parts shall become the property of Seller. Shipment to Buyer of repaired or replacement Products shall be made in accordance with the Delivery provisions of the Seller's Terms and Conditions of Sale.

Consumables are expressly excluded from this warranty. If Seller elects to repair defective medical device instruments, Seller may, in its sole discretion, provide a replacement loaner instrument to Buyer as necessary for use while the instruments are being repaired.

Notwithstanding the foregoing, Products supplied by Seller that are obtained by Seller from an original manufacturer or third party supplier are not warranted by Seller, but Seller agrees to assign to Buyer any warranty rights in such Product that Seller may have from the original manufacturer or third party supplier, to the extent such assignment is allowed by such original manufacturer or third party supplier.

In no event shall Seller have any obligation to make repairs, replacements or corrections required, in whole or in part, as the result of (i) normal wear and tear, (ii) accident, disaster or event of force majeure, (iii) misuse, fault or negligence of or by Buyer, (iv) use of the Products in a manner for which they were not designed, (v) causes external to the Products such as, but not limited to, power failure or electrical power surges, (vi) improper storage and handling of the Products or (vii) use of the Products in combination with equipment or software not supplied by Seller. If Seller determines that Products for which Buyer has requested warranty services are not covered by the warranty hereunder, Buyer shall pay or reimburse Seller for all costs of investigating and responding to such request at Seller's then prevailing time and materials rates. If Seller provides repair services or replacement parts that are not covered by this warranty, Buyer shall pay Seller therefor at Seller's then prevailing time and materials rates. ANY INSTALLATION, MAINTENANCE, REPAIR, SERVICE, RELOCATION OR ALTERATION TO OR

Terms and Conditions of Sale

OF, OR OTHER TAMPERING WITH, THE PRODUCTS PERFORMED BY ANY PERSON OR ENTITY OTHER THAN SELLER WITHOUT SELLER'S PRIOR WRITTEN APPROVAL, OR ANY USE OF REPLACEMENT PARTS NOT SUPPLIED BY SELLER, SHALL IMMEDIATELY VOID AND CANCEL ALL WARRANTIES WITH RESPECT TO THE AFFECTED PRODUCTS.

THE OBLIGATIONS CREATED BY THIS WARRANTY STATEMENT TO REPAIR OR REPLACE A DEFECTIVE PRODUCT SHALL BE THE SOLE REMEDY OF BUYER IN THE EVENT OF A DEFECTIVE PRODUCT. EXCEPT AS EXPRESSLY PROVIDED IN THIS WARRANTY STATEMENT, SELLER DISCLAIMS ALL OTHER WARRANTIES, WHETHER EXPRESS OR IMPLIED, ORAL OR WRITTEN, WITH RESPECT TO THE PRODUCTS, INCLUDING WITHOUT LIMITATION ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE. SELLER DOES NOT WARRANT THAT THE PRODUCTS ARE ERROR-FREE OR WILL ACCOMPLISH ANY PARTICULAR RESULT.

INDEMNIFICATION BY SELLER: Seller agrees to indemnify, defend and save Buyer, its officers, directors, and employees from and against any and all damages, liabilities, actions, causes of action, suits, claims, demands, losses, costs and expenses (including without limitation reasonable attorney's fees) ("Indemnified Items") for (i) injury to or death of persons or damage to property to the extent caused by the negligence or willful misconduct of Seller, its employees, agents or representatives or contractors in connection with the performance of services at Buyer's premises under this Agreement and (ii) claims that a Product infringes any valid United States patent, copyright or trade secret; provided, however, Seller shall have no liability under this Section to the extent any such Indemnified Items are caused by either (i) the negligence or willful misconduct of Buyer, its employees, agents or representatives or contractors, (ii) by any third party, (iii) use of a Product in combination with equipment or software not supplied by Seller where the Product would not itself be infringing, (iv) compliance with Buyer's designs, specifications or instructions, (v) use of the Product in an application or environment for which it was not designed or (vi) modifications of the Product by anyone other than Seller without Seller's prior written approval. Buyer shall provide Seller prompt written notice of any third party claim covered by Seller's indemnification obligations hereunder. Seller shall have the right to assume exclusive control of the defense of such claim or, at the option of the Seller, to settle the same. Buyer agrees to cooperate reasonably with the Seller in connection with the performance by Seller of its obligations in this Section.

Notwithstanding the above, Seller's infringement related indemnification obligations shall be extinguished and relieved if Seller, at its discretion and at its own expense (a) procures for Buyer the right, at no additional expense to Buyer, to continue using the Product; (b) replaces or modifies the Product so that it becomes non-infringing, provided the modification or replacement does not adversely affect the specifications of the Product; or (c) in the event (a) and (b) are not practical, refund to Buyer the amortized amounts paid by Buyer with respect thereto, based on a five (5) year amortization schedule. The foregoing indemnification provision states Seller's entire liability to Buyer for the claims described herein.

INDEMNIFICATION BY BUYER: Seller agrees to indemnify, defend and save Buyer, its officer, directors, and employees from and against any and all damages, liabilities, actions, causes of action, suits, claims, demands, losses, costs and expenses (including without limitation reasonable attorney's fees) ("Indemnified Items") for (i) injury to or death of persons or damage to property to the extent caused by the negligence or willful misconduct of Seller, its employees, agents or representatives or contractors in connection with the performance of services at Buyer's premises under this Agreement and (ii) claims that a Product infringes any valid United States patent, copyright or trade secret; provided, however, Seller shall have no liability under this Section to the extent any such Indemnified Items are caused by either (i) the negligence or willful misconduct of Buyer, its employees, agents or representatives or contractors, (ii) by any third party, (iii) use of a Product in combination with equipment or software not supplied by Seller where the Product would not itself be infringing, (iv) compliance with Buyer's designs, specifications or instructions, (v) use of the Product in an application or environment for which it was not designed or (vi) modifications of the Product by anyone other than Seller without Seller's prior written approval. Buyer shall provide Seller prompt written notice of any third party claim covered by Seller's indemnification obligations hereunder. Seller shall have the right to assume exclusive control of the defense of such claim or, at the

option of the Seller, to settle the same. Buyer agrees to cooperate reasonably with Seller in connection with the performance by Seller of its obligations in this Section.

Notwithstanding the above, Seller's infringement related indemnification obligations shall be extinguished and relieved if Seller, at its discretion and at its own expense (a) procures for Buyer the right, at no additional expense to Buyer, to continue using the Product; (b) replaces or modifies the Product so that it becomes non-infringing, provided the modification or replacement does not adversely affect the specifications of the Product; or (c) in the event (a) and (b) are not practical, refund to Buyer the amortized amounts paid by Buyer with respect thereto, based on a five (5) year amortization schedule. THE FOREGOING INDEMNIFICATION PROVISION STATES SELLER'S ENTIRE LIABILITY TO BUYER FOR THE CLAIMS DESCRIBED HEREIN.

Buyer shall indemnify, defend with competent and experienced counsel and hold harmless Seller, its parent, subsidiaries, affiliates and divisions, and their respective officers, directors, shareholders and employees, from and against any and all damages, liabilities, actions, causes of action, suits, claims, demands, losses, costs and expenses (including without limitation reasonable attorneys' fees and disbursements and court costs) to the extent arising from or in connection with (i) the negligence or willful misconduct of Buyer, its agents, employees, representatives or contractors; (ii) use of a Product in combination with equipment or software not supplied by Seller where the Product itself would not be infringing; (iii) Seller's compliance with designs, specifications or instructions supplied to Seller by Buyer; (iv) use of a Product in an application or environment for which it was not designed; or (v) modifications of a Product by anyone other than Seller without Seller's prior written approval.

SOFTWARE: With respect to any software products incorporated in or forming a part of the Products hereunder, Seller and Buyer intend and agree that such software products are being licensed and not sold, and that the words "purchase", "sell" or similar or derivative words are understood and agreed to mean "license", and that the word "Buyer" or similar or derivative words are understood and agreed to mean "licensee". Notwithstanding anything to the contrary contained herein, Seller or its licensor, as the case may be, retains all rights and interest in software products provided hereunder.

Seller hereby grants to Buyer a royalty-free, non-exclusive, nontransferable license, without power to sublicense, to use software provided hereunder solely for Buyer's own internal business purposes on the hardware products provided hereunder and to use the related documentation solely for Buyer's own internal business purposes. This license terminates when Buyer's lawful possession of the hardware products provided hereunder ceases, unless earlier terminated as provided herein. Buyer agrees to hold in confidence and not to sell, transfer, license, loan or otherwise make available in any form to third parties the software products and related documentation provided hereunder. Buyer may not disassemble, decompile or reverse engineer, copy, modify, enhance or otherwise change or supplement the software products provided hereunder without Seller's prior written consent. Seller will be entitled to terminate this license if Buyer fails to comply with any term or condition herein. Buyer agrees, upon termination of this license, immediately to return to Seller all software products and related documentation provided hereunder and all copies and portions thereof.

Certain of the software products provided by Seller may be owned by one or more third parties and licensed to Seller. Accordingly, Seller and Buyer agree that such third parties retain ownership of and title to such software products. The warranty and indemnification provisions set forth herein shall not apply to software products owned by third parties and provided hereunder.

LIMITATION OF LIABILITY: NOTWITHSTANDING ANYTHING TO THE CONTRARY CONTAINED HEREIN, THE LIABILITY OF SELLER UNDER THESE TERMS AND CONDITIONS (WHETHER BY REASON OF BREACH OF CONTRACT, TORT, INDEMNIFICATION, OR OTHERWISE, BUT EXCLUDING LIABILITY OF SELLER FOR BREACH OF WARRANTY (THE SOLE REMEDY FOR WHICH SHALL BE AS PROVIDED UNDER SECTION 7 ABOVE)) SHALL NOT EXCEED AN AMOUNT EQUAL TO THE LESSER OF (A) THE TOTAL PURCHASE PRICE THERETOFORE PAID BY BUYER TO SELLER WITH RESPECT TO THE PRODUCT(S) GIVING RISE TO SUCH LIABILITY OR (B) ONE MILLION DOLLARS (\$1,000,000). NOTWITHSTANDING ANYTHING TO THE CONTRARY CONTAINED HEREIN, IN NO

EVENT SHALL SELLER BE LIABLE FOR ANY INDIRECT, SPECIAL, CONSEQUENTIAL OR INCIDENTAL DAMAGES (INCLUDING WITHOUT LIMITATION DAMAGES FOR LOSS OF USE OF FACILITIES OR EQUIPMENT, LOSS OF REVENUE, LOSS OF DATA, LOSS OF PROFITS OR LOSS OF GOODWILL), REGARDLESS OF WHETHER SELLER (a) HAS BEEN INFORMED OF THE POSSIBILITY OF SUCH DAMAGES OR (b) IS NEGLIGENT.

EXPORT RESTRICTIONS: Buyer acknowledges that each Product and any related software and technology, including technical information supplied by Seller or contained in documents (collectively "Items"), is subject to export controls of the U.S. government. The export controls may include, but are not limited to, those of the Export Administration Regulations of the U.S. Department of Commerce (the "EAR"), which may restrict or require licenses for the export of Items from the United States and their re-export from other countries. Buyer shall comply with the EAR and all other applicable laws, regulations, laws, treaties, and agreements relating to the export, re-export, and import of any Item. Buyer shall not, without first obtaining the required license to do so from the appropriate U.S. government agency; (i) export or re-export any Item, or (ii) export, re-export, distribute or supply any Item to any restricted or embargoed country or to a person or entity whose privilege to participate in exports has been denied or restricted by the U.S. government. Buyer shall cooperate fully with Seller in any official or unofficial audit or inspection related to applicable export or import control laws or regulations, and shall indemnify and hold Seller harmless from, or in connection with, any violation of this Section by Buyer or its employees, consultants, agents, or customers.

PROMOTION CODE TERMS AND CONDITIONS: Discounts are valid on the purchase of list-price items only through fishersci.com orders. One-time use only. All promotions and discounts are on Fisher Scientific cart items only. Valid in the U.S. only. To redeem, enter the promo code in the box marked promo code at checkout. Free shipping offers apply to standard shipping only. Not valid with any other promotion. Terms are subject to change. Offer void where prohibited, licensed or restricted by federal, state, provincial or local laws or regulation or agency/institutional policy. Other restrictions may apply.

ACCEPTABLE PAYMENT METHODS: The Seller prefers to receive payment via ACH or other electronic interface methods that directly exchange funds between the Buyer's and Seller's bank accounts. The Seller also accepts checks mailed to one of its lockbox remittance locations. Although the Seller does accept credit card payments at the time of purchase, it does not accept credit card payments after the point of sale.

PROMOTIONAL TERMS FOR HEALTHCARE PROVIDERS AND FEDERAL, STATE AND LOCAL GOVERNMENT CUSTOMERS: Many promotions are not available to our current or potential healthcare customers or to federal, state and local government customers.

Healthcare customers include any healthcare practitioner, other healthcare provider or any individual or organization authorized to prescribe, dispense, purchase or influence the acquisition or use of medical devices or supplies for clinical use. Healthcare customers include, without limitation, any "Health Care Practitioner" under the Massachusetts Marketing Code of Conduct Law (defined at 105 C.M.R. §907.004) or a "Health Care Provider" under the Vermont Prescribed Products Gift Ban and Disclosure Law (defined at Vt. Stat. Ann. tit. 18, §4631a(8)). By participating in any promotion that is subject to the above limitations, Buyer warrants that it is not a current or potential healthcare customer or a federal, state and local government customer. Seller reserves the right to determine Buyer's status in the event of a dispute.

In the event that the promotion is available to Healthcare providers, Buyer acknowledges that the offer may include a discount or other price reduction that must be properly and accurately accounted for and reported by Buyer in accordance with all federal and state laws, including without limitation the federal anti-kickback law (42 C.F.R. § 1320a-7b(b) (3)(A)) and regulations thereunder (42 C.F.R. §1001.952(h)).

MISCELLANEOUS: (a) Buyer may not delegate any duties nor assign any rights or claims hereunder without Seller's prior written consent, and any such attempted delegation or assignment shall be void. (b) The rights and obligations of the parties hereunder shall be governed by and construed in accordance with the laws of the Commonwealth of Pennsylvania, without reference to its choice of law provisions. Each party hereby irrevocably consents to the exclusive jurisdiction of the state and federal courts located

in Allegheny County, Pennsylvania, USA, in any action arising out of or relating to this Agreement and waives any other venue to which it may be entitled by domicile or otherwise. (c) In the event of any legal proceeding between the Seller and Buyer relating to this Agreement, neither party may claim the right to a trial by jury, and both parties waive any right they may have under applicable law or otherwise to a right to a trial by jury. Any action arising under this Agreement must be brought within one (1) year from the date that the cause of action arose. (d) The application to this Agreement of the U.N. Convention on Contracts for the International Sale of Goods is hereby expressly excluded. (e) In the event that any one or more provisions contained herein shall be held by a court of competent jurisdiction to be invalid, illegal or unenforceable in any respect, the validity, legality and enforceability of the remaining provisions contained herein shall remain in full force and effect, unless the revision materially changes the bargain. (f) Seller's failure to enforce, or Seller's waiver of a breach of, any provision contained herein shall not constitute a waiver of any other breach or of such provision. (g) Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to humans or animals. (h) Seller shall cooperate with Buyer to monitor invoicing accuracy and will conduct appropriate internal reviews upon request. Reviews shall be limited to once per year and shall cover the prior twelve month period. Reasonable credit shall be given to undercharges and overcharges. If Buyer engages external consultants to review invoice accuracy, Seller reserves the right to charge a reasonable fee for support provided to such party. (i) Buyer agrees that all pricing, discounts and technical information that Seller provides to Buyer are the confidential and proprietary information of Seller. Buyer agrees to (1) keep such information confidential and not disclose such information to any third party, and (2) use such information solely for Buyer's internal purposes and in connection with the Products supplied hereunder. Nothing herein shall restrict the use of information available to the general public. (j) Any notice or communication required or permitted hereunder shall be in writing and shall be deemed received when personally delivered or three (3) business days after being sent by certified mail, postage prepaid, to a party at the address specified herein or at such other address as either party may from time to time designate to the other. (k) Seller may, in its sole discretion, provide (1) applicable Product training to Buyer or its employees, or (2) samples of Products to Buyer for distribution to patients of Buyer. Buyer agrees that any such samples shall be distributed to patients for patient use or, if not so distributed, returned to Seller. Buyer shall not use such samples to provide care to patient and shall not bill patients or third party payers for the provision of such samples.

ACCEPTABLE PAYMENT METHODS: The Seller prefers to receive payment via ACH or other electronic interface methods that directly exchange funds between the Buyer's and Seller's bank accounts. The Seller also accepts checks mailed to one of its lockbox remittance locations. Although the Seller does accept credit card payments at the time of purchase, it does not accept credit card payments after the point of sale.

MEDICARE/MEDICAID REPORTING REQUIREMENTS: If Buyer is a recipient of Medicare/Medicaid funds, Buyer acknowledges that it has been informed of and agrees to fully and accurately account for, and report on its applicable cost report, the total value of any discount, rebate or other compensation paid hereunder in a way that complies with all applicable federal, state and local laws and regulations which establish "Safe Harbor" for discounts. Buyer shall make written request to Seller in the event Buyer requires additional information from Seller in order to meet its reporting requirements. Buyer acknowledges that agreement to such reporting requirement was a condition precedent to Seller's agreement to provide Products and that Seller would not have entered into this Agreement had Buyer not agreed to comply with such obligations.

PRODUCT DESCRIPTIONS: Product Descriptions are provided by the manufacturer of the product and are current as of the date of printing of this catalog. More current descriptions provided by the manufacturers are reflected at fisheredu.com.

LOOK TO FISHER SCIENCE EDUCATION FOR HASSLE-FREE SERVICE • PROMPT DELIVERY • GREAT PRICES • QUALITY PRODUCTS AND SELECTION

FISHER SCIENCE EDUCATION GUARANTEE

At Fisher Science Education, we are committed to providing you with the highest quality products and services possible. If, for any reason, you are not 100% satisfied with your purchase, simply contact our friendly customer service team within 30 days of the invoice date. We will exchange the product, repair or replace the product or issue you a credit for the full purchase price. Simply call us, toll-free, for a Return Authorization Number. Special order items, furniture, and closeouts cannot be exchanged or credited.

HOW TO ORDER

Fisher Science Education offers you many ways to order. So we can serve you quickly, it helps to have your account number available when placing your order. We gladly accept purchase orders issued on School or District letterhead. Registered users may also place orders online at fisheredu.com. For your convenience, we also accept VISA™, MasterCard™, and American Express™ credit cards. For credit card purchases, be ready to provide the card number, the type of card, exact name on the card, expiration date, full address and telephone number.

Mail: Fisher Science Education
4500 Turnberry Drive
Hanover Park, IL 60133

Phone: 1-800-955-1177 • 7 a.m. to 5:30 p.m.,
Central Time – Monday through Friday

Fax: 1-800-955-0740 • 24 hours a day, 7 days a week

Email: fse.custserv@thermofisher.com

Internet: fisheredu.com

Special note on international purchases: Please contact Global Export Customer Service if your order requires export and if the ultimate destination is outside of the United States.

Fisher Scientific Latin America and Global Export Customer Service Center:

3970 John's Creek Court, Suite 500, Suwanee, GA 30024 USA

Telephone (inside the U.S.): 1-800-955-5090

Telephone (outside the U.S.): 770-871-4725

Fax (outside the U.S.): 770-871-4726

PRICES AND PAYMENT

All pricing subject to change.

If you don't have an account and would like one, we'll be happy to set up a user account for you — simply call Customer Service at 1-800-955-1177.

To complete your credit card, check, or money order payments, please include applicable sales tax and 10% of the total price of all products (minimum of \$15) purchased to cover shipping, handling and insurance

Please provide payment (net) within 30 days from the date of the invoice.

If you have any questions about product selection, pricing, or invoicing, please call us at 1-800-955-1177.

SPECIAL PURCHASES

Fisher Science Education will sell BALANCES, CHEMICALS and BACTERIAL CULTURES to educational institutions ONLY. Please submit orders for these products on school letterhead or order them through your registered user account at fisheredu.com.

We will honor your requests for tax-exempt purchases if your account is coded tax-exempt (a signed tax-exempt certificate is on file with Fisher Science Education) or, if purchasing with a credit card, the card is an official tax-exempt card.

Some of the products we sell are time sensitive and must be delivered within a specified period of time. Others may be considered hazardous materials. For time-sensitive materials, please specify the desired delivery date when you want the products to arrive so that you will be available to receive them. There is a charge for time-sensitive and hazardous materials. (See: Shipping Your Order.)

SHIPPING YOUR ORDER

We want your purchase to arrive promptly and undamaged. To ensure this, we only deliver products to a street address, not to a Post Office Box — please remember this when placing your order. Other things to consider for product shipping include:

How should we ship your purchase? We will ship according to your special instructions, whenever possible. Otherwise, we will select the best shipment method, based on the nature of the material, destination, package size and weight.

Do you need extra-quick delivery? Overnight shipping is available for many products at an additional cost, but certain hazardous materials may be exempt from this service — please ask your Customer Service Representative when placing your order.

Is motor freight necessary? Some items must be shipped by motor freight (rather than by small parcel carriers) and will have different shipping costs. These items are noted in our catalog with a "Motor Freight" icon. Call your Customer Service Representative for assistance in calculating these expenses.

Is the material hazardous? There is a single charge of \$27.50 per order for hazardous materials, no matter how many hazardous items are on your order.

Is your purchase live or time-sensitive? Be sure to specify the desired delivery date for all live material orders. Some live products have minimum purchase requirements, require special handling fees or have shipping restrictions. Contact Customer Service for specific details.

ONCE YOU RECEIVE YOUR ORDER

Inspect your shipment! Open and inspect your order immediately upon arrival and notify us of any problems. Report claims for damage within the seven (7) day period after delivery to allow us to remedy problems with shipping companies.

Want to return a product? The dedicated staff at Fisher Science Education Customer Service is committed to resolving any questions or problems you may encounter. Here are the steps to take:

- Please notify us no later than seven (7) days after delivery of any damaged or unsatisfactory shipments
- Obtain a return authorization number from Fisher Science Education Customer Service prior to returning any product.
- Provide the Fisher Science Education Confirmation Number, found in the upper left hand corner of the packing slip or invoice, or your account number and the purchase order number.

NOTE: Products are subject to a fifteen percent (15%) restocking charge, unless they were not supplied in accordance with your order or are defective at the time of delivery.

Products in this catalog are intended for use by children age 13 or over.

LIMITED WARRANTY

Fisher Scientific Company L.L.C. ("Fisher") will make available the manufacturer's warranties, without recourse to Fisher.

However, except as otherwise set forth here, Fisher expressly disclaims all other warranties, whether expressed, implied or statutory, including the warranties of merchantability and fitness for a particular purpose.

In no event shall Fisher be liable for any special, indirect, incidental, consequential or exemplary damages, however arising, even if Fisher Scientific has been advised of the possibility of such damages, out of the sale or use of the products described in this catalog.

Your sole and exclusive remedy for any cause of action arising out of the sale or use of any product described in this catalog shall be repair or replacement of the product or refund of the purchase price at Fisher's option.

©2024 Thermo Fisher Scientific Inc. All rights reserved.
For trademark ownership see Trademark Reference.
Printed and bound in the U.S.A. 23-920-1656
BN237490764-US

PROTOCOL SHOWER AND EYEWASH STATIONS

- Features an emergency drench shower
- Provides convenient storage for safety supplies
- Lower cabinet locks for security
- Eyewash unit includes lever action ball valve
- Available ADA model provides easy access
- 36"W x 22"D x 84"H



 **DIVERSIFIED**
SPACES™

Safety you can count on!

fisheredu.com/diversified



Healthcare Training and Education Supplies

Explore a complete range of healthcare education products to help prepare the nurses and allied health professionals of tomorrow.

Nursing

Find a range of tools to develop basic knowledge and learn advanced skills.

- Clinical Classroom Facilities
- Infection and Spill Control
- Patient Care Training


Allied Health

Train for specialized fields, like audiology and laboratory science.

- Primary and Emergency Care Education
- Diagnostic Education
- Health Science Specialties
- Other Specialty Training

Visit fisheredu.com/healthcare-education-products to learn more.

 **fisher science**
education
part of Thermo Fisher Scientific



Safety

2024 Product Catalog

Distributed by Fisher Science Education. Contact us today:

In the United States

Order online: fisheredu.com

Call customer service: 1-800-955-1177

Fisher Science Education

4500 Turnberry Drive

Hanover Park, IL 60133



© 2024 Thermo Fisher Scientific Inc. All rights reserved.

Trademarks used are owned as indicated at fishersci.com/trademarks.