

Semiconductor Grade Reagents Ultra High-Purity That Meets Your Needs

With over 30 years of experience in the production and purification of high purity chemicals and reagents, Honeywell produces a comprehensive portfolio for the electronics and semiconductor industry. Our wide base of products is proven and used by the leading companies producing electronic components in a large-scale.

Our high-purity chemicals are available in smaller package sizes specifically designed for scientists engaged in education, research, development, prototyping and small scale fabrication of high tech micro- and nanochips.

The semiconductor grade product range includes high purity products required for high performance applications:

- **Etchants** components required for wet etching processes using such as acids/bases, ammonium fluoride, and hydrogen peroxide.
- **Hexamethyldisilazane** (HMDS) to silanize the surface of silicon wafer
- **Solvents** with extremely low levels of metals are used extensively for cleaning equipment, drying wafers as well as substrate deposition or removal.

FEATURES


- Superior purity, stability and exceptional lot-to-lot consistency
- ISO 9001 and RC 14001 Certifications

PACKAGING

- 1 L glass bottle
- 2.5 L plastic bottles and 5 L plastic cans
- 5 kg plastic bottle

CHEMICALS INCLUDE

- Acids
- Bases
- Solvents
- Other electronic chemicals



Honeywell Cat. No.	Fisher Scientific Cat. No.	Product Name	Packaging
Acids/Bases			
40291H-2.5L	60-090-123	Ammonium hydroxide solution, ≥25% NH ₃ in H ₂ O, VLSI grade	2.5 L
40253H-2.5L	60-090-321	Hydrochloric acid, fuming 37%	2.5 L
40233H-2.5L	60-090-320	Hydrochloric acid, ≥32%	2.5 L
40213H-5L	60-090-330	Hydrofluoric acid, 49.5-50.5%	5 L
40222H-2.5L	60-090-416	Nitric acid, ≥69%	2.5 L
40230H-2.5L	60-090-415	Nitric acid, ≥65%	2.5 L
40303H-2.5L	60-090-418	Nitric acid, 69-71%, VLSI grade	2.5 L
40266H-2.5L	60-090-461	Phosphoric acid, ≥85%	2.5 L
40254H-2.5L	60-090-563	Potassium hydroxide	5 kg
Solvents			
40289H-2.5L	60-090-084	Acetone, ≥99.5%, USLI grade	2.5 L
40296H-5L	60-048-486	Methanol, ≥99.9% VLSI grade	5 L
40219H-5L	60-090-323	2-Propanol, ≥99.8%	5 L
40301H-2.5L	60-090-335	2-Propanol, ≥99.8% VLSI grade	2.5 L, 5 L
Other Electronic Chemicals			
40207H-2.5L	60-090-245	Ammonium fluoride-hydrofluoric acid mixture, AF 875-125, etching mixture	2.5 L
40208H-5L	60-090-122	Ammonium fluoride solution, ≥40%	5 L
40292H-5L	60-090-121	Ammonium fluoride solution, ≥40% VLSI grade	5 L
40215H-1L	60-090-299	Hexamethyldisilazane (HMDS), ≥98%	1 L
40267H-5L	60-090-331	Hydrogen peroxide solution, ≥30%	5 L

Contact us today:

In the United States

Order online: fishersci.com
 Fax an order: 1-800-926-1166
 Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca
 Fax an order: 1-800-463-2996
 Call customer service: 1-800-234-7437

