



Laboratory Equipment

Do More With OHAUS



Ingeniously Practical

AquaSearcher Bench Meters

For Smart pH and Conductivity Measurement

- Up to 0.001 pH measurement resolution
- 6.5-inch LCD display touch keypad (AB41 and 33 series)
- Measurements and calibrations made simple by straightforward menu.



AB41pH

AB33M1

AB23

Starter Portable Meters

For Versatile pH, Conductivity and DO Measurement

- Ergonomic, multifunctional design
- IP54 and IP67 rated protection against dust and water
- Suitable for field or laboratory applications



Starter 300
pH & ORP

Starter 300C
Conductivity & TDS

Starter 400D
Dissolved Oxygen

Starter 400M
pH & Conductivity

Starter Pen Meters

For Convenient pH, EC, TDS, Salinity, DO and ORP Measurement

- Superior OHAUS quality & design
- Simple and easy-to-use operation
- Wrist strap and IP67 waterproof design offer protection in the field



pH
Pen Meter

Conductivity
Pen Meter

Salinity
Pen Meter

TDS
Pen Meter

ORP
Pen Meter

DO
Pen Meter

Frontier 5000 Series Mini

Convenient Mini Centrifuge for Simple and Quick Life Science Separation Applications

- A quiet motor and rubber base assure quiet, well-balanced operation
- Dual lid locks and imbalance sensor ensure safety
- High max speed of 6,000 rpm in a small, compact footprint



Frontier FC5306

Frontier 5000 Series Micro

Microliter Centrifuge for High-Speed Separation Applications

- Easy to use control panel that supports simple operation
- High maximum g force of 21,953 x g for purification applications
- Seven rotor options, including aerosol tight lids



Frontier 5515

Frontier 5000 Series Multi

Multi-Function Centrifuges for high or low speed sample separations.

- Quickly program speed and time with easy-to-turn control dial
- Accommodate sample sizes from 0.2ml to 750mL
- Built-in safety features include imbalance sensor and secure lid lock



Frontier Multi Pro
5816R



Frontier Multi
5706

Hot Plate Stirrers

Superior Safety Features and Intelligent Performance

- High maximum temperature up to 500°C
- Top plate sizes of 4"×4", 7"×7", 10"×10" or round
- Easy to Read LCD Display with intuitive icons and large hot top indicator



Guardian 7000



Guardian 7000 Uni-Block



Guardian 5000

Incubating & Open Air Shakers

Precise Speed and Temperature Control to Protect Delicate Samples

- Wide variety of models provide application and motion versatility
- Broad assortment of accessories can accommodate most samples
- Precise Temperature Control between 15°C below Ambient up to 65°C



Incubating Cooling Thermal Shaker



Heavy Duty Orbital Shaker



Incubating Heavy Duty Orbital Shakers

Vortex Mixers

Provide Stable and Reliable Vortexing Action

- Analog and Digital models available for a wide range of applications
- Sturdy construction provides stable, reliable vortexing action
- Wide variety of accessories to accommodate most sample vessels



Heavy Duty Vortex Mixer



Analog Mini Vortex Mixer



Microplate Vortex Mixer

Dry Block Heaters

Versatile Block Heaters Provide Temperature Stability

- 1, 2, 4, and 6-block models, as well as heated lid options
- Digital and Analog models available
- Exceptional temperature uniformity of 0.1°C



2 Block Dry Block Heater with Lid



Digital 2 Block Dry Block Heater



Analog 1 Block Dry Block Heater

Bead Mill Homogenizer

For High Throughput Homogenization of Samples

- Models specific for high-throughput applications
- Color coded tube accessories accommodate different sample types
- Five pre-set programs optimized for speed and time



HT Lysing Homogenizer

Achiever™ 5000 Overhead Stirrers

Reliable Overhead Stirrers for highly viscous stirring applications

- Mix sample sizes up to 100 L
- Torque range from 20 Ncm to 200 Ncm
- Keyless chuck for quick shaft exchange



The Brand You Can Trust

The OHAUS product range is specifically designed to help maximize productivity, across every surface of the workspace. From the office to the warehouse, our Ingeniously Practical portfolio is packed with products made with your customers' needs in mind.

Our industry-leading line of scales and balances offer the accuracy, speed, and peace of mind your customers need to Weigh It with ease, while our ever-growing line of laboratory instruments products allows them to Test It with the confidence they need.

Introduced in 2017, the OHAUS line of laboratory equipment rounds out the ability to Do More in the lab, offering products ranging from mixers and shakers to clamps and supports – and everything in between.

For information visit www.ohaus.com



OHAUS CORPORATION

7 Campus Drive
Suite 310
Parsippany, NJ 07054
USA

Tel: 800.672.7722
973.377.9000

Fax: 973.944.7177

www.ohaus.com

211201_1 © Copyright OHAUS Corporation